



	10	9	8	7	6	5	4	3	2	1
	MATERIAL NUMBER	ALTERNATE NUMBER	STUD SIZE	"S" ±.005/(0.13)	"W" ±.010/(0.25)	"C" ±.009/(5.31)	"L" ±.038/(16.21)	PACKAGING		
F	191460016	B-307-04	4	.119/(3.02)	.245/(6.22)	.209/(5.31)	.638/(16.21)	LOOSE PIECE		
	191460017	B-307-06	6	.146/(3.71)	.245/(6.22)	.209/(5.31)	.638/(16.21)			
	191460018	B-324-04	4	.119/(3.02)	.295/(7.49)	.211/(5.36)	.635/(16.13)			
	191460019	B-324-06	6	.146/(3.71)	.295/(7.49)	.211/(5.36)	.635/(16.13)			
	191460021	B-324-08	8	.173/(4.39)	.295/(7.49)	.211/(5.36)	.635/(16.13)			
	191460024	B-327-06	6	.146/(3.71)	.362/(9.19)	.269/(6.83)	.770/(19.56)			
E	191460025	B-327-08	8	.173/(4.39)	.388/(9.85)	.269/(6.83)	.770/(19.56)	TAPE MOUNTED		
	191460096	B-327-10	10	.198/(5.03)	.388/(9.85)	.269/(6.83)	.770/(19.56)			
	191460065	B-307-04T	4	.119/(3.02)	.245/(6.22)	.209/(5.31)	.638/(16.21)			
	191460066	B-307-06T	6	.146/(3.71)	.245/(6.22)	.209/(5.31)	.638/(16.21)			
	191460068	B-324-04T	4	.119/(3.02)	.295/(7.49)	.211/(5.36)	.635/(16.13)			
	191460020	B-324-06T	6	.146/(3.71)	.295/(7.49)	.211/(5.36)	.635/(16.13)			
D	191460069	B-324-08T	8	.173/(4.39)	.295/(7.49)	.211/(5.36)	.635/(16.13)			
	191460070	B-327-06T	6	.146/(3.71)	.362/(9.19)	.269/(6.83)	.770/(19.56)			
	191460071	B-327-08T	8	.173/(4.39)	.388/(9.85)	.269/(6.83)	.770/(19.56)			
	191460072	B-327-10T	10	.198/(5.03)	.388/(9.85)	.269/(6.83)	.770/(19.56)			



PARTS ON TAPE



NOTES:
1. MATERIAL: COPPER .031/(.79) THICK.
2. PLATING: ELECTRO-TIN.
3. BRAZED SEAM.
4. ALL DIMENSIONS IN INCHES/(MM).

CUSTOMER DRAWING

DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR 1/2°		REVISE ONLY ON CAD SYSTEM													
<table><tr><th></th><th>INCH</th><th>METRIC</th></tr><tr><td>3 PLACE</td><td>± .005</td><td>± ---</td></tr><tr><td>2 PLACE</td><td>± .01</td><td>± 0.13</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± 0.25</td></tr></table>			INCH	METRIC	3 PLACE	± .005	± ---	2 PLACE	± .01	± 0.13	1 PLACE	± ---	± 0.25	TITLE SPADE TONGUE TERMINAL 16-14 AWG VERSAKRIMP, 300-SERIES	
	INCH	METRIC													
3 PLACE	± .005	± ---													
2 PLACE	± .01	± 0.13													
1 PLACE	± ---	± 0.25													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NO. DATE 1 OF 1 99/11/12													
DRWG. BY HEB APP'D. BY RWD		PART NO. SEE TABLE DRWG. NO. SD-19146-001													
CHK'D. BY RWD SCALE 4: 1		FILE NAME 19146001.DGN THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX-ETC INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.													
		DIV. SIZE ET B													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19146-0096](#)