



DUAL-IN-LINE SOCKETS

SERIES 110, 122, 123 • INTEGRAL DECOUPLING CAPACITOR • OPEN FRAME



- Low profile DIP sockets w/ integral decoupling capacitor: .1μ F 20%-50V multi-layer ceramic epoxy encapsulated. Temp. range: -25° C to +85° C
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 110, 122 and 123 use MM #1001, #0088 or #0089 pins. See pages 165 & 198 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION		
	A	B	C		Solder Tail	L = .370 (2 Level Wrappost)	L = .510 (3 Level Wrappost)
14	0.7	0.3	0.4	28	110-XX-314-41-801000	122-XX-314-41-801000	123-XX-314-41-801000
16	0.8	0.3	0.4	25	110-XX-316-41-801000	122-XX-316-41-801000	123-XX-316-41-801000
18	0.9	0.3	0.4	22	110-XX-318-41-801000	122-XX-318-41-801000	123-XX-318-41-801000
20	1.0	0.3	0.4	20	110-XX-320-41-801000	122-XX-320-41-801000	123-XX-320-41-801000
22	1.1	0.3	0.4	18	110-XX-322-41-801000	122-XX-322-41-801000	123-XX-322-41-801000
24	1.2	0.3	0.4	16	110-XX-324-41-801000	122-XX-324-41-801000	123-XX-324-41-801000
28	1.4	0.3	0.4	14	110-XX-328-41-801000	122-XX-328-41-801000	123-XX-328-41-801000
24	1.2	0.6	0.7	16	110-XX-624-41-801000	122-XX-624-41-801000	123-XX-624-41-801000
28	1.4	0.6	0.7	14	110-XX-628-41-801000	122-XX-628-41-801000	123-XX-628-41-801000
32	1.6	0.6	0.7	12	110-XX-632-41-801000	122-XX-632-41-801000	123-XX-632-41-801000
40	2.0	0.6	0.7	10	110-XX-640-41-801000	122-XX-640-41-801000	123-XX-640-41-801000
					XX=Plating Code See Below	RoHS-2 2011/65/EU	
SPECIFY PLATING CODE XX =					13	93	43
Sleeve (Pin)					10 μ" Au	200 μ" Sn/Pb	200 μ" Sn
Contact (Clip)					30 μ" Au	30 μ" Au	30 μ" Au

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[123-43-624-41-801000](#) [110-93-316-41-801000](#) [110-93-318-41-801000](#) [110-93-314-41-801000](#) [110-93-320-41-801000](#) [110-93-324-41-801000](#) [110-90-316-00-000000](#) [110-90-628-00-000000](#) [123-93-628-41-801000](#) [123-93-624-41-801000](#) [123-93-640-41-801000](#) [123-93-314-41-801000](#) [123-93-316-41-801000](#) [123-93-318-41-801000](#) [123-93-320-41-801000](#) [123-93-324-41-801000](#) [110-13-628-41-801000](#) [110-13-624-41-801000](#) [110-13-314-41-001100](#) [110-13-640-41-801000](#) [110-93-632-41-801000](#) [110-93-624-41-801000](#) [110-93-628-41-801000](#) [110-93-640-41-801000](#) [110-13-314-41-801000](#) [110-13-316-41-801000](#) [110-13-318-41-801000](#) [110-13-320-41-801000](#) [110-13-324-41-801000](#) [110-13-322-41-801000](#) [110-13-328-41-801000](#) [110-13-422-41-801000](#) [110-13-632-41-801000](#) [110-93-322-41-801000](#) [110-93-328-41-801000](#) [110-93-422-41-801000](#) [122-13-314-41-801000](#) [122-13-316-41-801000](#) [122-13-318-41-801000](#) [122-13-320-41-801000](#) [122-13-322-41-801000](#) [122-13-324-41-801000](#) [122-13-328-41-801000](#) [122-13-422-41-801000](#) [122-13-624-41-801000](#) [122-13-628-41-801000](#) [122-13-632-41-801000](#) [122-13-640-41-801000](#) [123-13-314-41-801000](#) [123-13-316-41-801000](#) [123-13-318-41-801000](#) [123-13-320-41-801000](#) [123-13-322-41-801000](#) [123-13-324-41-801000](#) [123-13-328-41-801000](#) [123-13-422-41-801000](#) [123-13-624-41-801000](#) [123-13-628-41-801000](#) [123-13-632-41-801000](#) [123-13-640-41-801000](#) [123-93-322-41-801000](#) [123-93-328-41-801000](#) [123-93-422-41-801000](#) [123-93-632-41-801000](#) [110-43-318-41-801000](#) [123-43-314-41-801000](#) [123-43-640-41-801000](#) [123-43-316-41-801000](#) [123-43-320-41-801000](#) [123-43-628-41-801000](#) [110-43-624-41-801000](#) [110-43-324-41-801000](#) [110-43-628-41-801000](#) [110-43-320-41-801000](#) [110-43-640-41-801000](#) [110-43-314-41-801000](#) [110-43-316-41-801000](#) [123-43-318-41-801000](#) [110-43-322-41-801000](#) [110-43-328-41-801000](#) [110-43-422-41-801000](#) [110-43-632-41-801000](#) [123-43-322-41-801000](#) [123-43-324-41-801000](#) [123-43-328-41-801000](#) [123-43-632-41-801000](#) [110-13-652-61-001000](#) [110-41-422-41-605000](#) [110-13-628-61-001000](#) [110-91-952-61-001000](#) [110-43-632-61-605000](#) [110-33-320-41-530000](#) [110-93-964-61-001000](#) [110-41-624-61-001000](#) [110-93-422-61-001000](#) [110-41-952-61-001000](#) [110-13-322-61-801000](#) [110-43-648-61-001000](#) [110-11-308-41-001000](#) [110-44-964-61-001000](#)