

BACKSHELLS FOR METAL SHELL "D" CONNECTORS 9 THROUGH 37 POSITIONS



PHYSICAL PROPERTIES

INSULATION MATERIAL: Glass filled thermoplastic, rated UL 94V-0

COLOR: Black.

INSULATION MATERIAL (SHIELDED): glass filled thermoplastic, rated 94V-0, chrome electroplated

ELECTRICAL PROPERTIES

SHIELDING EFFICIENCY: >40dB @ 100 MHz to 1 GHz


ENVIRONMENTAL PROPERTIES

TEMPERATURE RATING: -55°C to 125°C

APPLICATION TOOLING

HAND TOOL	779-2100
with Die (Flat Cable Outlet)	779-2173
with Die (Round Cable Outlet)	779-2174
BENCH PRESS (MANUAL)	779-3200
BENCH PRESS (PNEUMATIC)	779-3500XT
with Platen and Base Plate (Flat Cable Outlet)	779-3173
with Platen and Base Plate (Round Cable Outlet)	779-3174

- ① Use for screw set:
Mounting screw 609-004 with Jacksocket Assembly 609-003,
609-006-1 or 609-007-1



Ordering Information

CATALOG NUMBERS				FOR CONNECTOR TYPES SERIES 622	NO. OF POS. A	DIMENSIONS IN MM (INCHES)					
FLAT CABLE	BACKSHELL WITH CABLE OUTLET		ROUND CABLE (METALLIZED)			BACKSHELLS		ROUND CABLE		SHIELD Ø	
	ROUND CABLE	FLAT CABLE (METALLIZED)				B	MIN.	JACKET Ø MAX.	MIN.		
622-009D	622-009DR	622-009DM	622-009DRM	622-09PM, M1, M2 622-09SM, M1, M2	9	25.0 (.98)	37.5 (1.48)	4.6 (.18)	6.0 (.24)	2.8 (.11)	4.2 (.165)
622-015D	622-015DR	622-015DM	615-015DR	622-15PM, M1, M2 622-15SM, M1, M2	15	33.3 (1.31)	45.8 (1.80)	6.1 (.24)	7.6 (.299)	4.3 (.169)	5.8 (.228)
622-025D	622-025DR	622-025DM	622-025DRM	622-25PM, M1, M2 622-25SM, M1, M2	25	47.0 (1.85)	59.5 (2.34)	7.1 (.28)	8.8 (.35)	5.3 (.21)	7.0 (.276)
622-037D	622-037DR	622-037DM	622-037DRM	622-37PM, M1, M2 622-37SM, M1, M2	37	63.5 (2.50)	76.0 (2.99)	8.3 (.33)	9.8 (.386)	6.5 (.26)	8.1 (.32)