


TECHNICAL SPECIFICATIONS SC-Series

Material:	UL Recognised Plastic Material
Operating Temperature:	-55°C to +110°C
Cable Entry:	Top
Thumbscrews:	UNC 4-40
Cable O.D:	Up to 11,5mm
Colour:	Black or Light Grey

Also available in Shielded version, See page 23



Size	A	B	C
9-way	31,0	16,0	40,2
15-way	39,6	17,4	38,0
25-way	55,0	16,5	44,5
37-way	69,0	24,0	52,5
50-way	69,5	19,5	44,5

Ordering information - SHORT Jackscrews:

Size:	P/N - Kitted:	Product Code BLACK:
9-way	2360-0102-01	MHCCOV 9-SC-BK
15-way	2360-0102-02	MHCCOV15-SC-BK
25-way	2360-0102-03	MHCCOV25-SC-BK
37-way	2360-0102-04	MHCCOV37-SC-BK
50-way	2360-0102-05	MHCCOV50-SC-BK

Size:	P/N - Kitted:	Product Code LIGHT GREY:
9-way	2360-0102-11	MHCCOV 9-SC-LG
15-way	2360-0102-12	MHCCOV15-SC-LG
25-way	2360-0102-13	MHCCOV25-SC-LG
37-way	2360-0102-14	MHCCOV37-SC-LG
50-way	2360-0102-15	MHCCOV50-SC-LG

Ordering information - LONG Jackscrews:

Size:	P/N - Kitted:	Product Code BLACK:
9-way	2360-0102-21	MHCCOV 9-SCL-BK
15-way	2360-0102-22	MHCCOV15-SCL-BK
25-way	2360-0102-23	MHCCOV25-SCL-BK
37-way	2360-0102-24	MHCCOV37-SCL-BK
50-way	2360-0102-25	MHCCOV50-SCL-BK

Size:	P/N - Kitted:	Product Code LIGHT GREY:
9-way	2360-0102-31	MHCCOV 9-SCL-LG
15-way	2360-0102-32	MHCCOV15-SCL-LG
25-way	2360-0102-33	MHCCOV25-SCL-LG
37-way	2360-0102-34	MHCCOV37-SCL-LG
50-way	2360-0102-35	MHCCOV50-SCL-LG