




UPC Code : 078477515228

Country Of Origin : Mexico

**Available Colors :**



## 5623-2E

20 Amp, 120/277 Volt, Decora Plus Rocker 3-Way AC Quiet Switch, Commercial Spec Grade, Self Grounding, Back & Side Wired, - Black

Decora Plus devices combine designer styling with all the benefits of rugged Commercial Grade construction. The robust product offering includes: single pole, double pole, 3 and 4-way switches, momentary and maintained contact switches, as well as pilot light and illuminated switches.

### Technical Information

#### AC Horsepower Ratings

**HP Rating :** 1HP-120V 2HP-240V-277V

**Max. Amperage :** 16 Amp

#### Electrical Specifications

**Amperage :** 20 A

**Dielectric Voltage :** Withstands 1500V for 1 minute

**Endurance :** 50,000 cycles minimum

**Grounding :** Self-Grounding

**Overload UL20 Test :** 100 cycles of OL at 4.8 times rated current

**Temperature Rise :** Maximum 30 degrees C rise

**Voltage :** 120/277 VAC

#### Environmental Specifications

**Flammability :** Rated V-2 per UL 94

**Operating Temperature :** -40°C to 65°C

#### Material Specifications

**Actuator Material :** Thermoplastic

**Body Material :** Thermoplastic

**Color :** Ebony

**Strap Material :** Steel

#### Mechanical Specifications

**Product ID :** Stamped on Strap

**Terminal Accom. :** 14-#10 AWG back wired; #14-#12 AWG side wired

**Terminal ID :** Brass-Hot Black-Hot White-Neutral Green-Gnd

**Termination :** Back or Side Wire

**Torque Range :** 12-14 inch pounds

#### Product Features

**Body Material :** Thermoplastic

**Brand :** Decora Plus

**Color :** Ebony

**Device Type :** Rocker Switch

**Function :** 3-Way

**Grade :** Commercial Specification Grade

**Grounding :** Self-Grounding

**HP Rating :** 1HP-120V 2HP-240V-277V

**Voltage :** 120/277 VAC

#### Standards and Certifications

**ANSI :** C-73

**CSA C22.2 No. 111 :** File #152105


**NEMA :** WD-1 & WD-6

**NOM :** 057

**UL Standard :** UL 20


**Warranty :** 10-Year Limited

### Dimensional Diagram



### Wiring Diagram

#### 3-Way to 3-Way



### SPECIFICATION SUBMITTAL

|                      |                      |                      |
|----------------------|----------------------|----------------------|
| JOB NAME:            | CATALOG NUMBERS:     |                      |
| <input type="text"/> | <input type="text"/> | <input type="text"/> |
| JOB NUMBER:          | <input type="text"/> | <input type="text"/> |

#### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

#### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

#### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

#### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

