

LOC		DIST		REVISIONS						
AD		00		P	LTR	DESCRIPTION		DATE	DWN	APVD
					—	SEE SHEET 1		—	—	—

8	.775	.050	1.550	1.650	33	1.830	68	8-104069-8
	1.175	.050	2.350	2.450	49	2.630	100	8-104069-7
	.825	.050	1.650	1.750	35	1.930	72	8-104069-6
	—	.050	.950	1.050	21	1.230	44	8-104069-5
	—	.050	.700	.800	16	.980	34	8-104069-4
	—	.050	.500	.600	12	.780	26	8-104069-3
	—	.050	.450	.550	11	.730	24	8-104069-2
	—	.050	.250	.350	7	.530	16	8-104069-1
	—	.150	—	.300	6	.480	14	8-104069-0
	—	.125	—	.250	5	.430	12	7-104069-9
	—	.075	—	.150	3	.330	8	7-104069-8
	.675	.050	1.350	1.450	29	1.630	60	7-104069-7
	—	.050	.850	.950	19	1.130	40	7-104069-6
	—	.050	.600	.700	14	.880	30	7-104069-5
	—	.100	—	.200	4	.380	10	7-104069-4
	.925	.050	1.850	1.950	39	2.130	80	7-104069-3
	—	.050	1.100	1.200	24	1.380	50	7-104069-2
	—	.050	.350	.450	9	.630	20	7-104069-1
6	.775	.050	1.550	1.650	33	1.830	68	6-104069-8
	1.175	.050	2.350	2.450	49	2.630	100	6-104069-7
	.825	.050	1.650	1.750	35	1.930	72	6-104069-6
	—	.050	.950	1.050	21	1.230	44	6-104069-5
	—	.050	.700	.800	16	.980	34	6-104069-4
	—	.050	.500	.600	12	.780	26	6-104069-3
	—	.050	.450	.550	11	.730	24	6-104069-2
	—	.050	.250	.350	7	.530	16	6-104069-1
	—	.150	—	.300	6	.480	14	6-104069-0
	—	.125	—	.250	5	.430	12	5-104069-9
	—	.075	—	.150	3	.330	8	5-104069-8
	.675	.050	1.350	1.450	29	1.630	60	5-104069-7
	—	.050	.850	.950	19	1.130	40	5-104069-6
	—	.050	.600	.700	14	.880	30	5-104069-5
	—	.100	—	.200	4	.380	10	5-104069-4
	.925	.050	1.850	1.950	39	2.130	80	5-104069-3
	—	.050	1.100	1.200	24	1.380	50	5-104069-2
	—	.050	.350	.450	9	.630	20	5-104069-1
FINISH	F	E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN D. CLOUSER	10-3-88	 TE Connectivity			
				CHK T. ZOLA	10-3-88				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. ZOLA	10-3-88	NAME T. ZOLA	HEADER ASSEMBLY, RIGHT ANGLE, DOUBLE ROW, W/SIDE & END LATCHES, AMPMODU System 50		
		0 PLC ± .005		PRODUCT SPEC					
		1 PLC ± .005		108-1093					
		2 PLC ± .005		APPLICATION SPEC					
MATERIAL		ANGLES FINISH		114-25031		SIZE A1	CAGE CODE 00779	DRAWING NO 104069	RESTRICTED TO —
		SEE TABLE		WEIGHT —		CUSTOMER DRAWING			
						SCALE 4:1	SHEET 2	OF 2	REV AA