


4PB968



- 1 - UNIT INCLUDES 4IISM23 (GOLD BASIC SWITCH CONTACTS)
- 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 3 - 4IISM23 CONSTRUCTION PROVIDES SPLASH AND DUST RESISTANCE
- 4 - MOUNTING HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE	— — 2 - 5 LBS	CONTACT ARRANGEMENT		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
DIFFERENTIAL FORCE		2 X S P D T		ONE PLACE (. 0) ± . 030		
RELEASE FORCE		30 VOLTS DC RATING		TWO PLACE (. 00) ± . 015		
PRETRAVEL	— — .040 APPROX	INDUCTIVE ---SEA LEVEL-1/2 AMP 50,000 FT-1/2 AMP		THREE PLACE (. 000) ± . 005		
DIFFERENTIAL TRAVEL		RESISTIVE ---SEA LEVEL ---1 AMP 50,000 FT ---1 AMP		ANGLES ±		
OVERTRAVEL		MAXIMUM INRUSH -----2 AMP		WEIGHT		
FREE POSITION						
TOTAL TRAVEL	— — .100 APPROX					