




HONEYWELL PART NUMBER
BFLI-AWI-S

REV	DOCUMENT	CHANGED BY	CHECK
A	0018413	NM 18JAN06	RJ



NOTES
1 - 3X 6-32 UNC PRESSURE PLATE TERMINAL SCREWS
2 FURNISHED UNASSEMBLED

CHARACTERISTICS	CONTACT ARRANGEMENT
OPERATING POSITION:..... 15° MAX OPERATING FORCE:..... 7 OZ MAX	S P D T L162 5A 125, 250, 277 VAC 1/10 HP 250 VAC

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES X ± THIRD ANGLE PROJECTION 	.030 .015 .005	DRAWN	NM	16JAN06	Honeywell				
		CHECK	RJ	16JAN06					
		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL.			TITLE SWITCH, ENCLOSED				
		THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.							
		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
Pro/ENGINEER 3D			C	I	BFLI-AWI-S		A		
			SCALE 1:1		SHEET 1 OF 1				