




D

C

B

A



- 1

POLYESTER, FLAME RETARDANT, UL 94V-0 RATED, GLASS FILLED, BLACK.
- 2

SHIELD: BRASS; INSERT: ZINC ALLOY; BOARDLOCKS; COPPER ALLOY.
- 3

PHOSHOR BRONZE PER QQ-B-750.
- 4

.000030 MIN BRIGHT TIN-LEAD OVER .000050 MIN NICKEL.
- 5

.000150 MIN BRIGHT TIN-LEAD ON SOLDER END, .000050 MIN GOLD ON MATING END FOR A LENGTH OF .100 MIN ON MATING SURFACE, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- 6

GOLD PLATING PER MIL-G-45204, NICKEL PLATING PER QQ-N-290, TIN PLATING PER MIL-T-10727.
- 7

.000150 MIN NICKEL OVER .000100 MIN COPPER.
- 8

.000200 MIN TIN-LEAD OVER .000050 MIN NICKEL.

OBSOLETE	.630	1.050	.450	.660	.850	1.100	4	F	6-943036-1
	1.230	1.650	1.050	1.260	1.450	1.700	16	E	5-943036-6
	.830	1.250	.650	.860	1.050	1.300	8	E	5-943036-3
OBSOLETE	.730	1.150	.550	.760	.950	1.200	6	E	5-943036-2
	.630	1.050	.450	.660	.850	1.100	4	E	5-943036-1
OBSOLETE	1.230	1.650	1.050	1.260	1.450	1.700	16	D	4-943036-6
OBSOLETE	.830	1.250	.650	.860	1.050	1.300	8	D	4-943036-3
OBSOLETE	.730	1.150	.550	.760	.950	1.200	6	D	4-943036-2
	.630	1.050	.450	.660	.850	1.100	4	D	4-943036-1
OBSOLETE	1.230	1.650	1.050	1.260	1.450	1.700	16	C	3-943036-6
OBSOLETE	.830	1.250	.650	.860	1.050	1.300	8	C	3-943036-3
OBSOLETE	.730	1.150	.550	.760	.950	1.200	6	C	3-943036-2
	.630	1.050	.450	.660	.850	1.100	4	C	3-943036-1
OBSOLETE	1.230	1.650	1.050	1.260	1.450	1.700	16	B	2-943036-6
OBSOLETE	.830	1.250	.650	.860	1.050	1.300	8	B	2-943036-3
OBSOLETE	.730	1.150	.550	.760	.950	1.200	6	B	2-943036-2
	.630	1.050	.450	.660	.850	1.100	4	B	2-943036-1
	1.230	1.650	1.050	1.260	1.450	1.700	16	A	1-943036-6
	.830	1.250	.650	.860	1.050	1.300	8	A	1-943036-3
	.730	1.150	.550	.760	.950	1.200	6	A	1-943036-2
	.630	1.050	.450	.660	.850	1.100	4	A	1-943036-1
F	E	D	C	B	A	NO OF POSN	KEY LETTER	PART NO	

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON :
2 PLC DEC ± -
3 PLC DEC ± .005
ANGLES ± -

DR 1-27-89
J McCLINTON
CHK 2-8-89
R STONE
APPD 2-9-89
J PRITULSKY
APPD 2-9-89
D SUMMERS
PRODUCT SPEC
118-2047
APPLICATION SPEC
114-2081
WEIGHT -

AMP | AMP INCORPORATED
Harrisburg, Pa. 17105

NAME

RECEPTACLE ASSEMBLY,
SIDE ENTRY, SDL

SIZE **D** FSCM NO 00779 DRAWING NO 943036
SCALE 4:1 SHEET 1 OF 1