

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [30968-1208](#)
Status: **Active**
Overview: H-DAC 64™ Dual-Row High Density Automotive Connectors
Description: 2.54mm Pitch, 0.64mm Width HDAC 64™ High Density Automotive Crimp Housing, Dual Row, 20 Circuits, Polarization Option #2, Black

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-30968-0001 \(PDF\)](#)
[Product Specification PS-34646-001 \(PDF\)](#)
[Application Specification AS-30700-000 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)


General	
Product Family	Crimp Housings
Series	30968
Application	Power, Wire-to-Wire
Comments	Polarization Option #2
Overview	H-DAC 64™ Dual-Row High Density Automotive Connectors
Product Name	H-DAC 64™
UPC	822348869992

Physical	
Circuits (maximum)	20
Circuits Detail	20
Color - Resin	Black
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	8.206/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical	
Current - Maximum per Contact	7A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-30700-000
Product Specification	PS-30968-0001, PS-34646-001
Sales Drawing	SD-30968-120



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
30968Series

Mates With
30700 , 31389 H-DAC 64™ High Density Automotive Connectors

Use With
34230 Terminal

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

30968-1208