



TLS 2200® General Identification Materials:

B-498 Repositionable Vinyl Cloth Material

Color: White Finish: Semi-Gloss

Repositionable vinyl cloth material for wire, cable, and component marking. Adhesive and cloth backing offers excellent holding power, while easily being repositioned and removed.

Performance Attributes:




Figure 30




Figure 31




Figure 37



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Wire Gauge	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 31	PTL-10-498	B-498	Vinyl	White	0.250 (6.4)	0.750 (19.1)	16 to 10	1	750	R6210
Fig. 31	PTL-28-498	B-498	Vinyl	White	0.250 (6.4)	1.500 (38.1)	10 to 4	1	750	R6210
Fig. 30	PTLTB-498-318	B-498	Vinyl	White	0.318 (8.1)	30 ft. (9.1 m)	-	1	1 Roll Cont.	R6210
Fig. 31	PTL-16-498	B-498	Vinyl	White	0.375 (9.5)	1.000 (25.4)	12 to 10	1	500	R6210
Fig. 31	BPTL-11-498	B-498	Vinyl	White	0.500 (12.7)	0.750 (19.1)	16 to 10	1	5000	R6210
Fig. 31	BPTL-29-498	B-498	Vinyl	White	0.500 (12.7)	1.500 (38.1)	10 to 4	1	5000	R6210
Fig. 31	PTL-11-498	B-498	Vinyl	White	0.500 (12.7)	0.750 (19.1)	16 to 10	1	500	R6210
Fig. 37	PTL-7-498	B-498	Vinyl	White	0.500 (12.7)	0.500 (12.7)	22 to 16	1	500	R6210
Fig. 31	BPTL-18-498	B-498	Vinyl	White	0.750 (19.1)	1.000 (25.4)	12 to 10	1	2500	R6210
Fig. 31	PTL-18-498	B-498	Vinyl	White	0.750 (19.1)	1.000 (25.4)	12 to 10	1	250	R6210
Fig. 31	PTL-30-498	B-498	Vinyl	White	0.750 (19.1)	1.500 (38.1)	10 to 4	1	250	R6210
Fig. 37	BPTL-19-498	B-498	Vinyl	White	1.000 (25.4)	1.000 (25.4)	12 to 10	1	2500	R6210
Fig. 37	PTL-15-498	B-498	Vinyl	White	1.000 (25.4)	0.275 (7.0)	22 to 16	1	750	R6210
Fig. 37	PTL-17-498	B-498	Vinyl	White	1.000 (25.4)	0.500 (12.7)	12 to 10	1	500	R6210
Fig. 37	PTL-19-498	B-498	Vinyl	White	1.000 (25.4)	1.000 (25.4)	12 to 10	1	250	R6210
Fig. 31	PTL-21-498	B-498	Vinyl	White	1.000 (25.4)	2.500 (63.5)	Cables	1	100	R6210
Fig. 31	PTL-23-498	B-498	Vinyl	White	1.000 (25.4)	4.000 (101.6)	Cables	1	100	R6210
Fig. 31	PTL-31-498	B-498	Vinyl	White	1.000 (25.4)	1.500 (38.1)	10 to 4	1	250	R6210
Fig. 37	PTL-32-498	B-498	Vinyl	White	1.500 (38.1)	1.500 (38.1)	10 to 4	1	250	R6210
Fig. 31	PTL-33-498	B-498	Vinyl	White	1.500 (38.1)	4.000 (101.6)	Cables	1	100	R6210
Fig. 31	PTL-34-498	B-498	Vinyl	White	1.500 (38.1)	6.000 (152.4)	Cables	1	50	R6210

TLS 2200® General Identification Materials:

B-8425 Polypropylene Material

Color: White Finish: Gloss

White polypropylene material with glossy finish. An economical alternative to B-425. Designed for general purpose labeling, asset identification, rating plate and warning/instructional labeling.

Performance Attributes:




Figure 29




Figure 48



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 29	PTL-10-8425	B-8425	Polypropylene	White	0.750 (19.1)	0.250 (6.4)	1	750	R6010
Fig. 48	PTLFT-01-8425	B-8425	Polypropylene	White	1.180 (30.0)	0.788 (20.0)	1	250	R6010