

Catalog Number: LS-4.6-840A
Product ID: 7TAG009420R0013
UPC Number: 78621024219
EAN Number: 05414363074724
Status: A



Ball-Lock 304 Stainless Steel Cable Tie, Uncoated, for Temperatures up to 300 Degrees Celsius (572 F) for Indoor and Outdoor Applications, Suitable for High Temperature Environments, UL/EN/CSA62275 Type 2S Rated for AH-1 Plenum, Length of 840mm (33.10 Inches), Width of 4.75mm (0.187 inches), Thickness of 0.25mm (0.01 Inches), Tensile Strength Rating of 890 Newtons (200 Pounds)

- Application Tools: DAS-250

Actual

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5046 Stainless Steel Ties
Brand Name	Ty-Rap
Type	Ball-Lock 304 Stainless Steel Cable Tie
Standard	UL E49405
Width	0.187 in ; 4.75 mm
Length	33.1 in ; 840 mm
Bundle Diameter	0.25 to 10 in ; 6.3 to 254 mm
Material	304 Stainless Steel
Color	Metallic Gray
Lock Mechanism	Ball-Lock
Tensile Strength	200 pounds ; 890 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.75mm
Length belt/tape/tie	840mm
Tie thickness	0.25mm
Min. holding force	890N
Band closure	Ball latch
Material	Metal
Material quality	Stainless steel 304 (V2A)
Halogen free	Y
Colour	Stainless steel
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	1000
Outer Dimensions (inches)	37x5.75x4
Weight Uom	16.88 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001005
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com