


Standoffs Type B Female- / Male

- **Material** – Steel
– Brass
– Aluminum
– Stainless steel
- **Plating DIN 267**
– zinc plated 5 µm (A2E)
– yellow chromated 8 µm (A3G)
– nickel plated 3 µm (E1E)
– chromated
- **Tolerances**
– Hex length DIN 7168 middle
(in middle ±0,15 mm)
– Outside length ca. ±0,25 mm
– Thread DIN 13 Part 13
– Undercut DIN 76

DIN 1.0718
DIN 2.0402
DIN 3.1645.51
DIN 1.4305



M 3

Thread		Dimensions in mm			Steel		Brass		Alu		Steel	
GA	GI	L	I	A	zinc plated	yellow chrom.	nickel plated	nickel plated	chromated	stainless	under-	cut
					SW 5,5	SW 5,5	SW 5,5	SW 5	SW 5,5	SW 5,5		
M3	M3	4,0	2,5	6,0			5.13.041					no
M3	M3	5,0	2,5	5,0				5.13.058				no
M3	M3	5,0	2,5	6,0	5.13.051	5.13.054	5.13.053			5.13.059		yes
M3	M3	5,0	2,5	8,0			5.13.056	5.13.055				no
M3	M3	5,0	2,5	12,0				5.13.052				no
M3	M3	5,5	2,5	6,0			5.13.050					no
M3	M3	5,5	2,5	6,0		5.13.057						yes
M3	M3	6,0	2,5	6,0	5.13.061		5.13.063			5.13.069		yes
M3	M3	6,0	3,5	8,0			5.13.066					no
M3	M3	6,0	3,5	12,0				5.13.062				no
M3	M3	6,5	3,5	6,0	5.13.067							yes
M3	M3	7,0	4,5	6,0	5.13.071	5.13.072	5.13.073					yes
M3	M3	7,0	5,0	8,0			5.13.076					no
M3	M3	7,5	4,5	6,0	5.13.075	5.13.074						yes
M3	M3	8,0	5,0	6,0	5.13.081	5.13.084	5.13.083					yes
M3	M3	8,0	5,0	6,0						5.13.089		yes
M3	M3	8,0	5,0	8,0			5.13.086	5.13.085		5.13.088	5.13.908	no
M3	M3	8,5	6,0	6,0	5.13.082		5.13.087				5.13.080	yes
M3	M3	9,0	5,0	6,0							5.13.099	yes
M3	M3	9,0	6,0	6,0	5.13.091	5.13.094	5.13.093	5.13.095				yes
M3	M3	9,0	7,0	8,0			5.13.096					no
M3	M3	9,0	6,0	6,0			5.13.097					yes
M3	M3	10,0	6,5	6,0	5.13.101	5.13.104	5.13.103		5.13.108	5.13.109		yes
M3	M3	10,0	5,0	7,0			5.13.100					yes
M3	M3	10,0	6,5	8,0			5.13.102	5.13.105				yes
M3	M3	10,0	8,0	8,0			5.13.106					no
M3	M3	10,5	7,0	8,0	5.13.107*							yes
M3	M3	11,0	7,0	6,0	5.13.111	5.13.114	5.13.113			5.13.119		yes
M3	M3	11,0	7,5	10,5			5.13.112					no
M3	M3	11,0	8,0	8,0			5.13.116					no
M3	M3	12,0	7,0	6,0	5.13.121		5.13.123	5.13.120	5.13.128	5.13.129		yes
M3	M3	12,0	7,0	7,0		5.13.124						yes
M3	M3	12,0	7,0	8,0				5.13.125				no
M3	M3	12,0	8,0	8,0				5.13.126				no
M3	M3	12,5	7,0	6,0	5.13.127							yes
M3	M3	13,0	7,0	6,0	5.13.131	5.13.134	5.13.133					yes
M3	M3	13,0	8,0	8,0			5.13.136					yes
M3	M3	13,5	7,0	6,0	5.13.137	5.13.132				5.13.139		yes

* Nickel plated