



**Cordless - Drill and Drivers - 12 Volt 10 mm Cordless Drill Driver**

**DC740KA**



**DC740KA Features**

- Powerful 12 Volt drill driver for drilling and screwdriving applications
- Extremely compact and lightweight design for working in confined areas
- 10 mm single sleeve chuck and spindle lock for quick and easy bit change with one hand
- Ergonomically designed trigger and rubber grip for comfort and ease of use
- Two speed settings, variable speed and reverse switch for maximum control
- 14 Position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes
- Electric motor brake for added control
- All metal gearing for efficient power transmission and longer tool life
- Modular design for easy access to key components and excellent serviceability

**DC740KA Specifications**

|                                |                   |
|--------------------------------|-------------------|
| Voltage                        | 12 V              |
| Battery Capacity               | NiCd 1.3 Ah       |
| Chuck Capacity                 | 1.5-10 mm         |
| Power Output                   | 190 Watts         |
| No Load Speed                  | 0-350 /0-1200 rpm |
| Max Torque                     | 20 Nm             |
| Max. Drilling Capacity [Wood]  | 25 mm             |
| Max. Drilling Capacity [Metal] | 10 mm             |
| Spindle Thread                 |                   |
| Weight                         | 1.6 kg            |
| Length                         | 212 mm            |
| Height                         | 225 mm            |

**DC740KA Standard**

- 1 hour charger
- 2 batteries
- Heavy duty carrying case