

[Products](#)

[INTEL Cooler](#)

[AMD Cooler](#)

[DC-FAN](#)

[FB DIMM Heat](#)

[NB-Thermal](#)

[LED-Thermal](#)

[Cable](#)

You are here: [Home](#) > [Products](#) > [INTEL Cooler](#) > [INTEL BTX Solution](#)

INTEL Server Solution



Z6U440Y001

Z6U440Y001

Dempsey/Woodcrest 2U Tall Active Heatsink
SPECIFICATIONS

L x W x H: 88.9x78.7x67.0mm
Base Thickness: 7.0mm
Fin Thickness: 0.4mm
Fin Pitch: 1.60mm
Fin Number: 49 Fins
TIM: Dow Corning TG5022
Fan: 6020(suction)
Cooler RPM: 6800rpm
Weight: 510g

Thermal Performance :
AVC test result:
Res: 0.207 °C/W @ 15CFM
DP: 0.909 in H2O

Contact AVC



Head Office

AVC Taiwan

Kaoshiung

Tel : +886-7-815-7612

Fax : +886-7-812-0018