




LOC		DIST		REVISONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
B		ECO-07-021493		02OCT07	LAM	JW	

- MATERIAL: HOUSING - NYLON, COLOR: BLACK, UL 94V-0. OVERMOLDED TERMINAL ARRAY - PBT, BROWN. TERMINALS - 0.33[.013] THICK PHOS BRONZE PLATED WITH 1.27 μ m[.000050] MINIMUM HARD GOLD IN LOCALIZED AREA AND 3.81 μ m[.000150] MINIMUM TIN-LEAD IN SOLDER AREA OVER 1.27 μ m[.000050] MINIMUM NICKEL UNDERPLATE. SHIELD - 0.254[.010] THICK COPPER ALLOY PLATED WITH 2.03 μ m[.000080] MINIMUM THICK BRIGHT TIN OVER 1.27 μ m[.000050] MINIMUM NICKEL
- a** JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
- 3** USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN PRODUCING THESE PCB HOLES.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - DOCKS CHK J. WESTMAN APPV S. FLICKINGER 10JUN2005 10JUN2005		Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		MODULAR JACK ASSEMBLY, 8 POSITION, RIGHT ANGLE, LOW PROFILE, 8 PORT, CATEGORY 5	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± - ± - ANGLES ± - ± -		PRODUCT SPEC 108-1163-2		SIZE	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		APPLICATION SPEC 114-2048		CAGE CODE A1 00779	
CUSTOMER DRAWING				DRAWING NO C=6116525		RESTRICTED TO	
				WEIGHT -		SCALE 4:1	
						SHEET 1 OF 1	
						REV B	