

317 Pocket Digital Thermometer

Test the TPI advantage



Features:

- Air tip
- Field calibrateable to $\pm 2^{\circ}\text{F}$
- Rugged and waterproof (IP63)
- 3.1mm stem for "Pete's" plug
- Auto off
- Magnetic clip perfect for air duct applications
- 3-year limited warranty

APPLICATIONS:

HVACR

- Ambient Air
- Calibrate

Thermostats

- Vents
- Compressor Heads
- Registers

ELECTRICAL

- Motor Temperatures
- Transformer Temperatures

Faster response in air



Specifications:	
Temperature Range	-58°F to 300°F (-50°C to 150°C)
Accuracy	$\pm 2^{\circ}\text{F}$ ($\pm 1^{\circ}\text{C}$)
Resolution	0.1°F/°C
Sample Rate	1 reading every 1.5 second
Stem Length	2.8"
Tip Type	Air
Water Resistant	N/A
Water Proof	N/A
°C / °F Selectable	Yes
Data Hold	Yes
Auto Off	Yes
Battery Type	LR44

