


DC Power Jacks






16PJ031, 16PJ032

KOBI CONN

DC Power Jacks



16PJ031 A=ø2.0mm.004
16PJ032 A=ø2.35mm.004



Dimensions: in.

SPECIFICATIONS

Dielectric strength:	250VAC for 1 minute
Contact resistance:	30mΩ max. @ 1A
Insulation resistance:	50MΩ min. @ 500VDC
Insulation withstand voltage:	250VAC for 1 minute
Insertion & extraction force:	.8~2 Kg
Life Test:	100,000 cycles
Plastic:	polycarbonate (including 5% glass)
Operating temperature:	-10°C to +70°C
Storage temperature range:	-20°C to +70°C
Humidity test:	90-95% 40°C ±2°C (45 hours)
Soldering heat test:	solder temperature: 260°C±5°C dip time: 5±1 second
Tolerance:	± 0.3mm (.0118)

Date Last Revised: 5/19/09

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300037

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

16PJ031, 16PJ032

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

16PJ031 16PJ032