

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301080097](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Super-Safeway Twin Tube 64W Fluorescent Work Light 12V, Cord Type 12/3 SJOOW Feed Thru 7.62m (25.0') Cord Length

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374  
 UL E174254

**General**

Product Family Portable Lighting  
 Series [130108](#)  
 NEMA Configuration Non-NEMA  
 Outlet Feed-Through  
 Overview [Wide-Area Lighting Products](#)  
 Product Name Super-Safeway  
 Type Wide Area Lamps  
 UPC 78678867066

**Physical**

Cord Length - Primary 7.62m (25.0')  
 Cord Length - Secondary 0.152m (6.00" )  
 Depth 190.75mm (7.510")  
 Duty Industrial  
 Guard Included No  
 Guard Type N/A  
 Height 82.55mm (3.250")  
 Length 1.39m (54.620")  
 Material - Globe Butyrate  
 Material - Guard Nitrile Rubber 80 Shore A  
 Mounting Style Adjustable Brackets  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Fluorescent  
 Cord Type - Primary 12/3 SOOW  
 Lamp Type F32/T8  
 Lamp Wattage - Maximum 64W  
 Lumens 5300  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 12V AC/DC

**Material Info**

Engineering Number 1051-12



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130108 Series](#)