




Visit AVX's Website at www.avxcorp.com

Radial/SkyCaps




AVX Style	Width (W)	Height (H)	Thickness (T)	Lead Spacing (LS)	Lead Diameter (LD)
SR15	3.810 (0.150)	3.81 (0.150)	2.540 (0.100)	2.54 (0.100)	0.508 (0.020)
SR20	5.080 (0.200)	5.08 (0.200)	3.175 (0.125)	2.54 (0.100)	0.508 (0.020)
SR21	5.080 (0.200)	5.08 (0.200)	3.175 (0.125)	5.08 (0.200)	0.508 (0.020)
SR27	6.604 (0.260)	6.35 (0.250)	4.060 (0.160)	7.62 (0.300)	0.508 (0.020)
SR30	7.620 (0.300)	7.62 (0.300)	3.810 (0.150)	5.08 (0.200)	0.508 (0.020)
SR40	10.160 (0.400)	10.16 (0.400)	3.810 (0.150)	5.08 (0.200)	0.508 (0.020)

Stock No.	Mfr.'s Type	Cap. pF	Voltage	Tol.	Temp. Coefficient	EACH			
						1-24	25-99	100-499	500-Up
881-5100	SR305A103JAA	10000	50	5	NPO	1.63	1.11	.91	.75
881-3400	SR151A100JAA	10	100	5	NPO	.51	.28	.21	.16
881-5106	SR211A100JAA	10	100	5	NPO	.58	.33	.25	.18
881-5110	SR151A150JAA	15	100	5	NPO	.46	.26	.20	.13
881-5112	SR211A150JAA	15	100	5	NPO	.58	.33	.25	.18
881-5114	SR151A180JAA	18	100	5	NPO	.51	.28	.21	.16
881-5118	SR151A220JAA	22	100	5	NPO	.33	.18	.13	.10
881-5122	SR151A270JAA	27	100	5	NPO	.51	.28	.21	.16
881-3402	SR151A330JAA	33	100	5	NPO	.51	.28	.21	.16
881-5126	SR151A390JAA	39	100	5	NPO	.51	.28	.21	.16
881-3403	SR151A470JAA	47	100	5	NPO	.51	.28	.21	.16

Axial Leaded

Stock No.	Mfr.'s Type	Cap. pF	Voltage	Tol.	Temp. Coefficient	Dimensions—mm				EACH*
						Length (L)	Dia. (D)	Lead Dia.	Lead Length	
881-5276	SA105A102JAA	1000	50	5	NPO	4.32	2.54	0.483	25.4	.49
881-5284	SA101A221JAA	220	100	5	NPO	4.32	2.54	0.483	25.4	.43
881-5288	SA101A331JAA	330	100	5	NPO	4.32	2.54	0.483	25.4	.43
881-5308	SA102A220JAA	22	200	5	NPO	4.32	2.54	0.483	25.4	.41
881-5312	SA102A330JAA	33	200	5	NPO	4.32	2.54	0.483	25.4	.41
881-5314	SA102A470JAA	47	200	5	NPO	4.32	2.54	0.483	25.4	.41
881-5320	SA102A101JAA	100	200	5	NPO	4.32	2.54	0.483	25.4	.41
881-5322	SA102A121JAA	120	200	5	NPO	4.32	2.54	0.483	25.4	.41
881-5324	SA105C103KAA	10000	50	5	X7R	4.32	2.54	0.483	25.4	.59
881-5326	SA105C103KAA	10000	50	10	X7R	4.32	2.54	0.483	25.4	.40
881-5328	SA105C223KAA	22000	50	10	X7R	4.32	2.54	0.483	25.4	.43
881-5330	SA205C333KAA	33000	50	10	X7R	6.60	2.54	0.483	25.4	.53
881-5334	SA205C473KAA	47000	50	10	X7R	6.60	2.54	0.483	25.4	.55
881-5336	SA305C104KAA	100000	50	10	X7R	7.37	3.81	0.483	25.4	.76
881-5338	SA305C224KAA	220000	50	10	X7R	7.37	3.81	0.483	25.4	1.14
881-5344	SA101C102JAA	1000	100	5	X7R	4.32	2.54	0.483	25.4	.40
881-5346	SA101C222KAA	2200	100	10	X7R	4.32	2.54	0.483	25.4	.40
881-5350	SA101C472KAA	4700	100	10	X7R	4.32	2.54	0.483	25.4	.40
881-5358	SA102C471KAA	470	200	10	X7R	4.32	2.54	0.483	25.4	.40
881-5360	SA205E104MAA	100000	50	20	Z5U	6.60	2.54	0.483	25.4	.35
881-5368	SA305E474MAA	470000	50	20	Z5U	7.37	3.81	0.483	25.4	.81

*Sold only in multiples of 500.



For Fast, Dependable Service, Make Just One Call — 1-800-433-5700

ALLIED ► 575