

**LP4K0901BW3**

Miniature Contactor (TeSys K) Non-Reversing,  
9A(AC3) 20A(AC1), 3-Pole

List Price \$110.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

**Technical Characteristics**

Horsepower Rating (3-Phase)	2HP@200VAC - 3HP@230VAC - 5HP@460/575VAC
Inductive Amperes (AC3)	9A
Resistive Amperes (AC1)	20A
Approvals	UL Listed File E164862 NLDX2 - CSA Certified File LR43364 Class 3211 04 - IEC Rated 60947 - CE Marked
Auxiliary Contacts	1 N.C.
Horsepower Rating (1-Phase)	0.5HP@115VAC - 1.5HP@230VAC
Marketing Trade Name	TeSys
Integral Coil Suppression	Yes
Maximum Voltage Rating	600VAC
Number of Poles	3-Pole
Coil Voltage	24VDC (Low Consumption)
Contactor Type	Non-Reversing
Mounting Type	Panel
Terminal Type	Screw Clamp
Type	TeSys K
Width	1.77 Inches
Depth	2.24 Inches
Height	2.28 Inches
Weight	0.52 Pounds

**Shipping and Ordering**

Category	22321 - Contactors, DC, Open, Non-Reversing, K-Line
Discount Schedule	I12
GTIN	00785901641728
Package Quantity	1
Weight	0.49 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.