



THIS DRAWING IS UNPUBLISHED, RELEASED FOR PUBLICATION, 19


© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P/F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓		A	RELEASED P.A.R	2-20-85	RLT/ 67
✓		B	REVISED AF-1152	9/12/85	JSC/ 47
		C	REVISED PER 063A-0109-02	05 MAR 02	MSF /



FITS .125 DIA PIN

SECT. A-A



SECT. B-B

- 1 - DIMENSIONS IN BRACKETS ARE IN INCHES
2 - CONTINUOUS STRIP ON REELS
3 PRELIMINARY - NOT FOR PRODUCTION.

METRIC

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .010$ 0.25 ANGLES $\pm$	TIN	[22-18] 0.3-0.8 mm ²	3 63381-2
	NONE	[22-18] 0.3-0.8 mm ²	63381-1
CONTRACT NO DR <i>J.R. Pust</i> 12/18/84 CHK <i>G. Yetter</i> 12/18/84	FINISH	WIRE SIZE	PART NO
	MATERIAL [.014] 0.36 BRASS	NAME .125 DIA. PIN RECEPTACLE	
FINISH SEE TABLE	APPD <i>J. H. Gentry</i> 12/20/84 DSGN APPD OTHER APPD	SIZE B	FSCM NO 00779
		DRAWING NO 63381	SHEET