


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
ECPG-2G	.57 LB/10 PCS (260 G/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. ACCEPTS TWO NEMA STANDARD "GFCI" SWITCHES AND RECEPTACLES.
3. FOUR (4) #6 - 32 X 1/4 SCREWS ARE PROVIDED WITH FACEPLATE.
4. ALL DIMENSIONS IN PARENTHESES ARE IN METRIC.



CAD FILENAME/LAYERS										D35544B0_ECPG2G-C_00																						
										PANDUIT CORP. TINLEY PARK, ILLINOIS EXECUTIVE DOUBLE GANG GFCI FACEPLATE (ECPG-2G) CUSTOMER DRAWING																						
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±					UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.																	
										DRAWN BY		JBA		MAT'L:		SCALE					HALF											
R	7-23-96	JBA	RELEASED TO PRODUCTION.					35544-14							DATE		7-23-96		ABS					DRAWING No.		35544-14			DWG		A	
REV	DATE	BY	CHK	DESCRIPTION					ECN	CHK	CUST	SUP	CHECKED BY												SIZE							