

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
					F	REV PER ECR 07-023647	12OCT07	JR	TM

1.80 [.070]

BODY

SLEEVE

9.90 [.390] MIN

23.70 [.933] MAX

1.80 [.070]

2

3

AMP WIRE RANGE		FILE E13288	
16-14 AWG STRANDED		16-14 AWG STRANDED	

1 WIRE INSULATION DIA. 2.92-4.32 [.115-.170] DIA.

2 MATERIAL: BODY - CU PER ASTM B152 SLEEVE - CU PER ASTM B152 INSULATION - NYLON

3 FINISH: BODY - TIN PL. PER ASTM B545 SLEEVE - TIN PL. PER ASTM B545 INSULATION - COLOR - BLUE

4 LOOSE PIECE P/N 165172

4000		ON TAPE		696274-2	
QTY		PACKAGE TYPE		PART NO	

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221° F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 01DEC00		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK T MICHIELUTTI 01DEC00	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.0-2.6mm² [1,974-5,131] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		APVD T MICHIELUTTI 01DEC00	
FOR ORDER ENTRY		1-800-526-5142		MATERIAL		- 2		- 3	
		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						NAME	
								PRODUCT SPEC	
								APPLICATION SPEC	
								WEIGHT -	
								SIZE A3	
								CAGE CODE 00779	
								DRAWING NO C-696274	
								RESTRICTED TO -	
								SCALE 6:1	
								SHEET 1 OF 1	
								REV F	

CUSTOMER DRAWING