









		35.56 [1.400]	14	37.69 [1.484]	30	6-146130-4
E		33.02 [1.300]	13	35.15 [1.384]	28	6-146130-3
		30.48 [1.200]	12	32.61 [1.284]	26	6-146130-2
		27.94 [1.100]	11	30.07 [1.184]	24	6-146130-1
		25.40 [1.000]	10	27.53 [1.084]	22	6-146130-0
		22.86 [.900]	9	24.99 [.984]	20	5-146130-9
		20.32 [.800]	8	22.45 [.884]	18	5-146130-8
		17.78 [.700]	7	19.91 [.784]	16	5-146130-7
		15.24 [.600]	6	17.37 [.684]	14	5-146130-6
		12.70 [.500]	5	14.83 [.584]	12	5-146130-5
		10.16 [.400]	4	12.29 [.484]	10	5-146130-4
		7.62 [.300]	3	9.75 [.384]	8	5-146130-3
		5.08 [.200]	2	7.21 [.284]	6	5-146130-2
		2.54 [.100]	1	4.67 [.184]	4	5-146130-1
E		17.78 [.700]	7	19.91 [.784]	16	1-146130-8
E		5.08 [.200]	2	7.21 [.284]	6	1-146130-7
		35.56 [1.400]	14	37.69 [1.484]	30	1-146130-4
E		33.02 [1.300]	13	35.15 [1.384]	28	1-146130-3
		30.48 [1.200]	12	32.61 [1.284]	26	1-146130-2
		27.94 [1.100]	11	30.07 [1.184]	24	1-146130-1
D		25.40 [1.000]	10	27.53 [1.084]	22	1-146130-0
		22.86 [.900]	9	24.99 [.984]	20	146130-9
		20.32 [.800]	8	22.45 [.884]	18	146130-8
		17.78 [.700]	7	19.91 [.784]	16	146130-7
		15.24 [.600]	6	17.37 [.684]	14	146130-6
		12.70 [.500]	5	14.83 [.584]	12	146130-5
		10.16 [.400]	4	12.29 [.484]	10	146130-4
		7.62 [.300]	3	9.75 [.384]	8	146130-3
		5.08 [.200]	2	7.21 [.284]	6	146130-2
		2.54 [.100]	1	4.67 [.184]	4	146130-1
PLATING	C	B	A	NO OF POSN	PART NUMBER	

RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: J.KNAUB 30-09-94 CHK: G. DUBNICZKI 30-09-94		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± ± - ANGLES		NAME AFVD 30-09-94 G. DUBNICZKI PRODUCT SPEC — APPLICATION SPEC —	
		SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, DOUBLE ROW, .100 X.100 CL, .025 SQ.POST		SIZE —	
MATERIAL 		FINISH SEE TABLE		CASE CODE A1 00779	
		WEIGHT —		DRAWING NO C-146130	
		CUSTOMER DRAWING		RESTRICTED TO —	
				SCALE 8:1 SHEET 1 of 1 REV L	