








Diagram of a rectangular component with a circular feature (possibly a hole or a button) on the left side. A label "SEALING TAPE" points to a line on the top edge of the component.

Technical drawing of a rectangular block. A dimension line on the right indicates a height of $.295 \pm .020$.

- | | | | | | | |
|---|----------|---|---|------------|-------------|-------------|
|  | OBSOLETE | FIG 7 |  | .58 | 5 | 8-5435668-7 |
| | | FIG 2 | FIG 1 | .58 | 5 | 3-5435668-5 |
| | | | | .48 | 4 | 3-5435668-4 |
| | | | | .38 | 3 | 3-5435668-3 |
|  | OBSOLETE | | | 1.28 | 12 | 3-5435668-2 |
|  | OBSOLETE | | | 1.18 | 11 | 3-5435668-1 |
| | | | | 1.08 | 10 | 3-5435668-0 |
| | | | | .98 | 9 | 2-5435668-9 |
| | | | | .88 | 8 | 2-5435668-8 |
| | | | | .78 | 7 | 2-5435668-7 |
| | | | | .28 | 2 | 2-5435668-6 |
|  | OBSOLETE | | .68 | 6 | 2-5435668-5 | |
| | | |  | 1.08 | 10 | 5435668-9 |
| | | |  | .88 | 8 | 5435668-7 |
| | | |  | .68 | 6 | 5435668-5 |
| | |  | .58 | 5 | 5435668-4 | |
| | |  | .48 | 4 | 5435668-3 | |
|  | OBSOLETE |  | .28 | 2 | 5435668-1 | |
| | MARKING | SEALING TAPE | A | NO OF POSN | PART NO | |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BSV		08JAN05		 TE Connectivity	
		CHK —		—			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, LOW PROFILE	
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		PRODUCT SPEC — APPLICATION SPEC —		SIZE A2	
MATERIAL		FINISH		WEIGHT		CAGE CODE	
				—		DRAWING NO	
				A2		00779	
						C-5435668	
						RESTRICTED TO	
						—	
CUSTOMER DRAWING						SCALE 4:1	
						SHEET 1 of 2	
						REV A2	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN
			—	SEE SHEET 1	—	—




FIG 2





FIG 7

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BSV		08JAN05		 TE Connectivity	
		CHK —		—			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME	
		0 PLC ± —		PRODUCT SPEC		SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, LOW PROFILE	
		1 PLC ± —		—			
		2 PLC ± —					
		3 PLC ± —					
		4 PLC ± .005		APPLICATION SPEC			
		ANGLES ± —		—			
MATERIAL —		FINISH —		WEIGHT —		RESTRICTED TO —	
				A2 00779		C=5435668	
				CUSTOMER DRAWING		SCALE 4:1 SHEET 2 of 2 REV A2	