



Fittings for metallic conduits with plastic coating

• PCS-PC Plain Hole Connector, IP54

Plain hole connector, nickel plated brass.

Features and Benefits

- Two part fitting comprising shell and body without thread
- The body is fitted to the conduit through the opposite side of the entry
- Acts as a locking device
- Provides a smooth entry bush

Technical Table

Article-No.	Type	Nominal Ø	Pack Cont.
166-31200	PCS10-PC	10	10
166-31201	PCS12-PC	12	10
166-31202	PCS16-PC	16	10
166-31203	PCS20-PC	20	10
166-31204	PCS25-PC	25	10
166-31205	PCS32-PC	32	2
166-31206	PCS40-PC	40	2
166-31207	PCS50-PC	50	1
166-31208	PCS63-PC	63	1
166-31209	PCS75-PC	75	1

All dimensions in mm. Subject to technical changes.



HelaGuard PCS-PC Plain Hole Connector.

Material Data

Material	Nickel Plated Brass (NPB)
Colour	Metal (ML)
Operating Temperature	-100 °C to +300 °C



• PCS-FF Fixed Internal Thread, IP54

Fixed internal thread, nickel plated brass.

Features and Benefits

- Two part fitting comprising shell and body with internal thread
- Can be used to couple two pieces of conduit together when used with a swivel fitting

Technical Table

Article-No.	Type	Nominal Ø	Thread Size (metric)	Pack Cont.
166-31300	PCS16-FF-M20	16	M20	10
166-31301	PCS20-FF-M20	20	M20	10
166-31302	PCS25-FF-M25	25	M25	10
166-31303	PCS32-FF-M32	32	M32	10

All dimensions in mm. Subject to technical changes.



HelaGuard PCS-FF Fixed Internal Thread.