



► Products

► Design Resources

► Technical Info

► Global Sales

► News/Events

---Useful Links---

Quick Reference

Search by part #

go

Check distributor
part inventory

Stock Check

CLICK HERE!

Products

Browse Products

-By Device-

-By Product Line-

-Attachment Methods-

-Interface Materials-

-Accessories-

Useful Links

[MSDS Safety Sheets](#)

[How to Order?](#)

[Find Sales Rep](#)

[Find Distributor](#)

[Sample Request](#)

[Quote Request](#)

[Catalog Request](#)





[Building a Part #](#)

[Part # Cross Ref](#)

Accessories







Standard Mounting Pads






The following Mounting Pads are for use with TO-5



7717-167DAPG RoHS ✓ Compliant (DAP) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 3.18 (0.125)	
7717-167NG RoHS ✓ Compliant (nylon) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 3.18 (0.125)	
7717-161DAPG RoHS ✓ Compliant (DAP) Leads: 4-Mar Outside Diameter mm (in): 8.64 (0.340) Thickness: 1.91 (0.075)	
7717-161NG RoHS ✓ Compliant (nylon) Leads: 4-Mar Outside Diameter mm (in): 8.64 (0.340) Thickness: 1.91 (0.075)	
7717-159NG RoHS ✓ Compliant (nylon) Leads: 5	

Outside Diameter mm (in): 9.53 (0.375) Thickness: 5.59 (0.220)	
7717-158TG RoHS Compliant (Teflon) Leads: 4 Outside Diameter mm (in): 9.91 (0.390) Thickness: 0.25 (0.010)	
7717-131DAPG RoHS Compliant (DAP) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.97 (0.038)	
7717-131NG RoHS Compliant (nylon) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.97 (0.038)	
7717-114NG RoHS Compliant (nylon) Leads: 4 Outside Diameter mm (in): 9.02 (0.355) Thickness: 1.17 (0.046)	
7717-4DAPG RoHS Compliant Product Change Notice (DAP) Leads: 4 Outside Diameter mm (in): 9.53 (0.375)	

Thickness: 1.91 (0.075)	
7717-4NG (nylon) Leads: 4 Outside Diameter mm (in): 9.53 (0.375) Thickness: 1.91 (0.075)	
7717-5DAPG (DAP) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 3.18 (0.125)	
7717-5NG (nylon) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 3.18 (0.125)	
7717-15DAPG (DAP) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.51 (0.020)	
7717-15NG (nylon) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.51 (0.020)	

7717-3DAPG RoHS  Compliant Product Change Notice  (DAP) Leads: 4-Mar Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075)	
7717-3NG RoHS  Compliant Product Change Notice  (nylon) Leads: 4-Mar Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075)	
7717-79DAPG RoHS  Compliant Product Change Notice  (DAP) Leads: 3 Outside Diameter mm (in): 9.02 (0.355) Thickness: 0.97 (0.038)	
7717-79NG RoHS  Compliant Product Change Notice  (nylon) Leads: 3 Outside Diameter mm (in): 9.02 (0.355) Thickness: 0.97 (0.038)	
7717-178DAPG RoHS  Compliant Product Change Notice  (DAP) Leads: 3 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.53 (0.021)	
7717-178NG RoHS  Compliant Product Change Notice  (nylon) Leads: 3 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.53 (0.021)	

RoHS  Compliant Product Change Notice  7717-86DAPG (DAP) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075)	
RoHS  Compliant Product Change Notice  7717-86NG (nylon) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075)	
RoHS  Compliant 7717-22NG (nylon) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075)	
RoHS  Compliant 7717-22DAPG (DAP) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075)	
RoHS  Compliant 7717-238NG (nylon) Leads: 4-Mar Outside Diameter mm (in): 10.16 (0.400) Thickness: 4.06 (0.160)	
RoHS  Compliant 7717-300NG (nylon) Leads: Universal	

Outside Diameter mm (in): 11.18 (0.440)	
Thickness: 9.65 (0.380)	 Technical drawing of a TO5 package. The top view shows an outer diameter of $\varnothing 11.18 \pm .25$ (0.440 ± .010) and an inner diameter of $\varnothing 4.83$ (.190). The side view shows a thickness of $1.65 \pm .25$ (0.065 ± .010) and a base diameter of $\varnothing 8.13 \pm .25$ (0.320 ± .010). The cross-sectional view shows a base thickness of 1.52 (.060) and a total height of 9.65 (.380). The base has three typical places for mounting pads, each with a width of .76 (.030).
7717-94NG RoHS  Compliant	 Technical drawing of a TO5 package. The top view shows an outer diameter of 5.33 DIA (.210) and an inner diameter of .97 (.038). The side view shows a thickness of .43 (.017) and a base diameter of 8.89 DIA (.350). The base has four typical places for mounting pads, each with a radius of .43 (.017).
(nylon)	
Leads: 4-Mar	
Outside Diameter mm (in): 8.89 (0.350)	
Thickness: 0.97 (0.038)	