


PRODUCT NO.
SEE TABLE



mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family QUICKIE
ltr	ecr	no	dr	date	tolerances unless otherwise specified		title
G	V71133	SAR	9/25/97		angles linear .XX±.01/.3		30 AWG SOLID DOUBLE
H	V82043	RGD	11/12/98		linear .xxx±.005/.13		SCALLOPE PVC ROUND CAND. CABLE
J	M06-0282	MHT	7/26/06		linear .xxx±.0020/.05		dwg no 76167 sheet 1 of 2 size A3
							type Product Customer Drawing
sheet index	revision sheet	J	J				
		1	2				

PRODUCT NO.	NO. OF POS.	DIM "A"	TOLERANCE	DIM "B"	TOLERANCE	MIN. FT/M PER REEL
76167-009	9	.400/10.16	±.007/0.18	.450/11.43	±.010/0.25	100/30.48
↑ -010	10	.450/11.43	↑	.500/12.70	↑	↑
-014	14	.650/16.51		.700/17.78		
-015	15	.700/17.78	↓	.750/19.05	↓	
-016	16	.750/19.05	±.007/0.18	.800/20.32	±.010/0.25	
-020	20	.950/24.13	±.009/0.23	1.000/25.40	±.015/0.38	
-025	25	1.200/30.48	↑	1.250/31.75	↑	
-026	26	1.250/31.75	↑	1.300/33.02	↑	
-034	34	1.650/41.91	↓	1.700/43.18		
-037	37	1.800/45.72	±.009/0.23	1.850/46.99		
-040	40	1.950/49.53	±.011/0.28	2.000/50.80		
-044	44	2.150/54.61	↑	2.200/55.88		
-050	44	2.450/62.23	↓	2.500/63.50		
↓ -060	60	2.950/74.93	↓	3.000/76.20	↓	↓
76167-064	64	3.150/80.10	±.011/0.28	3.200/81.28	±.015/0.38	100/30.48

NOTES:

- MADE IN ACCORDANCE WITH PRODUCT SPEC BUS-12-001.
PURCHASE SPEC BUS-10-001.
- COLOR TO BE LIGHT BLUE WITH DARK BLUE TRACER
ON EDGE OF FIRST POSITION.
- UL LISTED STYLE 2651. CSA CERTIFIED (LATEST REVISION).

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family QUICKIE
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale NTS 	title
J					angles linear .XX±.01/.3		30 AWG SOLID DOUBLE
					0'±2' .xxx±.005/.13		SCALLOPE PVC ROUND CAND. CABLE
					xxxx±.0020/.05		dwg no sheet 2 of 2 size
				dr	S.ROYER 9/25/97		76167 A3
				enr	M.SMYK 9/25/97		
				chr	M.SMYK 9/25/97		
				appd	M.SMYK 9/25/97		
sheet index	revision sheet						type Product Customer Drawing