

TYSONIC

NON-SPILLABLE SEALED RECHARGEABLE BATTERY



TY1223 12V, 2.3Ah

☆ SPECIFICATION


- NOMINAL VOLTAGE : 12 V
- NOMINAL CAPACITY(20 hrs) : 2.3 Ah
- DIMENSIONS
 - TOTAL HEIGHT : 67 mm (2.64 inches)
 - CONTAINER HEIGHT : 60 mm (2.36 inches)
 - LENGTH : 178 mm (7.01 inches)
 - WIDTH : 35 mm (1.38 inches)
- WEIGHT : APPROX 0.95 Kg (2.09 lbs)
- MAX DISCHARGE CURRENT : 23 A (5 sec)
- STANDARD TERMINALS : FO-01
- CONTAINER MATERIAL : GENERAL GRADE ABS

☆ CHARACTERISTICS

- CAPACITY 25 C / 77 F
 - 20 hr @ 0.115 A : 2.3 Ah
 - 5 hr @ 0.21 A : 2.1 Ah
 - 1 hr @ 0.37 A : 1.84 Ah
 - 1 C @ 0.138 A : 1.40 Ah
- INTERNAL RESISTANCE() : 60 mΩ @ 25°C, 77 F Ω
- CHARGING VOLTAGE (25C , 77 F°)
 - STANDBY USE : 2.2750.025 V/CELL
 - : (-3.3mV / C / CELL)
 - CYCLE USE : 2.450.05 V/CELL
 - : (-5 mV / C / CELL) °
- MAX CHARGING CURRENT : 0.69 A



☆ Dimensions



☆ Terminal

