



LOC		DIST		REVISIONS			
DY		F	LTR	DESCRIPTION		DATE	OWN
				P		REVISED PER ECO-11-005139	19MAR11 RK HMR







MATING FACE




DETAIL D

- 1 SHIELD & CONTACTS: COPPER ALLOY.
HOUSING: POLYESTER, UL 94V-0 RATED, BLACK.
- 2 0.76 μm [0.000030] MIN GOLD FOR A LENGTH OF 1.27 [0.050] MIN FROM MATING END, 3.05 μm [0.000120] MIN MATTE-TIN ON OPPOSITE END, BOTH OVER 1.27 μm [0.000050] MIN NICKEL.
- 3 1.50-4.00 μm [0.000059-.000158] THICK BRIGHT TIN.
- 4 GOLD PLATING PER MIL-G-45204, TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 5 DATUMS AND BASIC DIMENSION SUPPLIED BY CUSTOMER.



DETAIL F
SCALE 50:1



RECOMMENDED PC BOARD LAYOUT
BOTTOM VIEW

P/N: 5750071-1 AS SHOWN

DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWG WYLEE 05JAN2005		REV SF LEONG	
9 PLC 1 PLC 5 PLC 4 PLC ANGLES		± ± ±0.13 [0.005] ± ±0°		PRODUCT SPEC 108-1225		NAME RECEPTACLE ASSY, FRONT PANEL GROUNDING, 6 POS, RIGHT ANGLE, MINIATURE CIRCULAR DIN	
MATERIAL 1		FINISH 2 3 4		WEIGHT -		SIZE A1	
CUSTOMER DRAWING		CAGE CODE 00779		DRAWING NO 5750071		SCALE 5:1	
				SHEET 1		OF 1	
				REV P			