



Standard Barrel Copper Lug

T&B Catalog Number:

53223M

UPC Number:

78621086891

Status:

Active

Description:

Cast Copper Two-Hole Heavy Duty Lug - Straight Standard Barrel - max 35KV, 750 kcmil Wire, 1/2 Bolt Size, 1 3/4 in. Hole Spacing, Tin Plated Blind End, Purple 112

Features

Electro Tin-Plated for Corrosion Resistance. Chamfered Barrels Provide Ease of Strand Entry and Inspection hole facilitates full insertion of the conductor.

Cable Area Clearly Identified on Lug.

General

Style	Heavy-Duty
Material	Cast Copper
Finish	Tin Plated
Wire Size	750 kcmil
Number of Studs	2
Stud Size (inches)	1/2
Bolt Hole Spacing	1 3/4
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	N
Marking	Standard
Hole Shape	Round
Die Color	Purple
Die Code	112

Dimension Information

A (inches)	5 5/16
B (inches)	3 1/2
C (inches)	1 5/8
D (inches)	17/32
E (inches)	1 23/64
F (inches)	5/8
H (inches)	1 3/4

Specifications

Temperature Rating	105°C
Voltage Rating	600V

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	140 lbs. per 100

Application Support

Overview	Available on Website
----------	----------------------



Notes

Dimensions given for reference only. Dimensions may vary up to +/- .030.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com