



UNIT:mm




CABLE WHITE PRINT
USB CABLE E189529  AWM 2725 VW-1 30V 80°C 28AWG/1PR AND 28AWG/2C

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 5 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑧ PE BAG				1/5	CLEAR SIZE: 330*380*0.05mm PRINT BLACK"MADE IN CHINA".			
⑦ PE BAG				1	CLEAR SIZE: 210*280*0.05mm PRINT BLACK"MADE IN CHINA".			
⑥ TIE				1	BLACK L=120mm			
⑤ OUT JACKET				6g	BLACK PVC-40P (MOULD NO: WM-40)			
④ OUT JACKET				6g	BLACK PVC-40P (MOULD NO: WM-88)			
③ CABLE				1	BLACK USB1.1 UL2725 28#/1P+28#/2C+AEB OD: 3.8mm L=5000 ± 15mm			
② CONN				1set	USB A MALE SHELL: NICKEL PIN: G/F 4PCS TYPE INSULATOR COLOR: WHITE			
① CONN				1set	USB MINI 5P MALE SHELL: NICKEL PIN: G/F 3PCS INSULATOR COLOR: BLACK			
NO. NAME				Q' TY	SPECIFICATION			

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	101-1031-BL-00500
DECIDED		DATE	2012-02-16
VERSIONS/EDITION	A/0	PROJECTION	