

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0982660318

Status:

Active

Overview:

Premo-Flex Cable Jumpers

Description:

0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 51.00mm Cable Length, Tin (Sn) Plating, 30 Circuits



Documents:

Drawing (PDF)

Product Specification PS-98266-001-001 (PDF)

Packaging Specification PK-98266-001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable
Series	98266
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	756054772744
Physical	
Cable Length	51.00mm
Circuits (Loaded)	30
Material - Plating Mating	Tin
Net Weight	0.529/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-98266-001-001
Product Specification	PS-98266-001-001
Sales Drawing	SD-98266-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/88/2018 (15	
January 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

98266 Series

Mates With

Easy-On FFC/FPC Connector:

524353033 , 541043033 , 524373033 ,
541323033 , 5019513 000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION