

4

3

2




1

SPECIFICATIONS:

CONTACT RATING: 3A @ 125 VAC OR 28 VDC (RESISTIVE)
 INITIAL CONTACT RESISTANCE: 20 MILLIOHMS MAXIMUM
 INSULATION RESISTANCE: 1000 MEGOHMS MINIMUM @ 500 VDC.
 DIELECTRIC STRENGTH: 1000 VOLTS RMS AT SEA LEVEL
 LIFE EXPECTANCY: 10,000 CYCLES AT FULL RATED LOAD
 CONTACTS: SOLID SILVER
 SEAL-TOGGLE: PER MIL-S-83731A
 STATIC: PARAGRAPH 4.8.20
 DYNAMIC: PARAGRAPH 4.8.20

REVISIONS

REV	DESCRIPTION	DATE	APPROVED
D	0G3C-0194-05	27MAR07	MZ



TTE23P-8T 1/4	2 TO 1 5 TO 4	OFF	2 TO 3 5 TO 6
TTF23N-8T 1/4	2 TO 1 5 TO 4	NONE	2 TO 3 5 TO 6
TTF13F-8T 1/4	2 TO 1	OFF	2 TO 3
TTF13D-8T 1/4	2 TO 1	NONE	2 TO 3
SWITCH NO.	FLAT	FLAT	FLAT

TERMINALS CONNECTED WHEN TOGGLE IS IN POSITION SHWN
 NOTE: TERMINAL DESIGNATION NUMBERS ARE FOR REFERENCE ONLY AND DO NOT APPEAR ON SWITCHES NOS 4, 5, 6 FOR D.P. VERSION ONLY.

AUGAT D/N 40210

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES
 TOLERANCES ON:
 .010 DECIMALS
 3 PL. DECIMALS ± .010
 ANGLES ±
 FRACTIONS

SIGNATURES

DATE

DRAWN

CHECKED

ENGRG

ISSUED

INSPECT PER
ALCO QAS 100

SYMBOL

A.Q.L.

□

CRITICAL

△

MAJOR

NONE

MINOR

THIRD ANGLE PROJECTION



DISTRIBUTION

1	2	3	4	5	6	7	8	9	10
---	---	---	---	---	---	---	---	---	----

tyco
Electronics

CUSTOMER DRAWING - TOGGLE SWITCH

SEALED SP & DP
TTE13(*)-8T 1/4

SIZE: SC. NO.

DWG. NO.

1437563-6

REV.

D

SCALE 4/1

SHEET OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TTE13E8T1/4](#)