

FEATURES

- 20A rating
- Compact package
- Choice of two mounting brackets
- Class B coil construction
- Approximate Size 2.42" x 2.07" x 1.31" h

Mounting Options: Panel Mount.



Mfr.'s Type	Coil			Contacts	
	Input	Res In Ohms	Nom. Power	Arrangement	Amp Rating

Enclosed Relay

KAP-5AG-120	120	2,250	2VA	SPDT	10
KAP-5AY-24	24	472	1.2W	SPDT	10
KAP-11AY-24	24	85	2VA	DPDT	5
KAP-11AY-120	120	2,250	2VA	DPDT	10
KAP-11AG-24	24	85	1.2W	DPDT	5
KAP-11AG-120	120	2,250	1.2W	DPDT	10
KAP-11DY-12	12	120	2VA	DPDT	5
KAP-11DY-24	24	472	2VA	3PDT	10
KAP-11DY-110	110	10,000	1.2W	3PDT	5
KAP-11DG-24	24	472	1.2W	3PDT	10
KAP-11DG-110	110	10,000			
KAP-14AY-120	120	2,250			
KAP-14AG-120	120	2,250			
KAP-14DY-24	24	472			
KAP-14DG-12	12	120			
KAP-14DG-24	24	472			

KAP-5DG-24 "P" denotes polycarbonate cover with octal-style plug.

KAP-5AG-24 "A" denotes AC coil

KAP-5DG-24 "D" denotes DC coil

KA-5AY-24 "Y" denotes Ag contacts

KA-5AG-24 "G" denotes AgCdO contacts

Note: Open style KRelays mount via a # 6-32 threaded stud and a locating tab on .438 centers. Tab requires .165" dia. clearance hole.


Enclosed KAP relays have a seated height of 2.281" and are 1.531" wide and 1.437" deep

KUHP Series Power Relays

FEATURES

- 20-30A rating
- Enclosed Case
- Various mounting options
- 3,750Vrms coil-to contact breakdown
- Class B coil construction
- Approximate Size 1.53" x 1.41" x 1.97" h

Mounting Options: Panel Mount, side or top mount



Mfr.'s Type	Coil			Contacts	
	Input	Res In Ohms	Nom. Power	Arrangement	Amp Rating

Enclosed Relay

KUHP-5A51-24	24	72	2.7VA	SPDT	30
KUHP-5A51-120	120	1,700			
KUHP-5AT1-120	124	1,700	2.7VA	SPDT	30
KUHP-5D51-12	12	120	1.2W	SPDT	30
KUHP-5D51-24	24	472			
KUHP-5DT1-12	12	120	1.2W	SPDT	30
KUHP-5DT1-24	24	472			
KUHP-11A51-24	24	72	2.7VA	DPDT	20
KUHP-11AT1-120	120	1,700	2.7VA	DPDT	20
KUHP-11D51-12	12	120	1.2W	DPDT	20
KUHP-11D51-24	24	472			
KUHP-11DT1-12	12	120	1.2W	DPDT	30
KUHP-11DT1-24	24	472			

KUHP-11A51-24 "A" denotes AC coil

KUHP-11D51-24 "D" denotes DC coil

KUHP-11A51-120 "5" denotes side mtg. brackets. Mounts on 2.5" centers


KUHP-11AT1-120 "T" denotes top mtg. brackets. Mounts on 1.875" centers

PM Series Power Relays

FEATURES

- 25A rating
- 4PDT Arrangement
- High dielectric Strength
- Screw or quick connect terminals
- Approximate Size 3.39" x 2.66" x 2.72" h

Mounting Options: Panel Mount.



Mfr.'s Type	Coil			Contacts	
	Input	Res In Ohms	Nom. Power	Arrangement	Amp Rating
PM17AY-24	24	5			
PM17AY-120	120	120	14VA	4PDT	25
PM17AY-240	240	587			
PM-17DY-12	2	33			
PM-17DY-24	24	132	4.4W	4PDT	25
PM-17DY-110	110	2,760			
PMT17DY-24	24	132	4.4W	4PDT	25


PM-17DY-24 "PM" denotes screw terminal type

PMT-17DY-24 "PMT" denotes .25" quick connect terminal type

PM Dust Covers

Mfr.'s Type	Description	Length	Width	Height
35D203	Plastic Cover	3.394 (86.21)	2.657 (67.49)	2.791 (69.06)
35D227	Metal Cover	5.313 (134.95)	3.831 (96.85)	3.813 (96.85)

35D227



35D203

