


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:


1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

										FIBER OPTIC PATCH CORD DUPLEX ST TO LC CONFIGURATION CUSTOMER DRAWING	
											 PANDUIT TM CORP. TINLEY PARK, ILL 60477
										 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (.0.3) (.XX) ± .03 (.0.8) ANGLES
										DRAWING FILENAME M02779BF_DC_00A.prt	SCALE NONE
										PART NO. SEE TABLE, SHT. 2	
										DRAWING NO. 02779-14 (SHT. 1 of 2)	SIZE A
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-14					DRAWN BY MC	REVIEW DRAWING NUMBERS
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	DATE 04-27-07	
										CHK'D	

DUPLEX ST TO LC FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				ST CONNECTOR			LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	COLOR	MAX. IL	MIN. RL	COLOR
FXE2-10M*Y	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 1.6mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH	0.30dB	26dB	ELECTRIC IVORY
F5E2-10M*Y		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F6E2-10M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F9E2-10M*Y		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH	0.35dB	55dB	BLUE
FXPE2-10M*	PLENUM (OFNP)	10 GbE 50/125um OM3	DUPLEX 1.6mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH	0.30dB	26dB	ELECTRIC IVORY
F5PE2-10M*		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F6PE2-10M*		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F9PE2-10M*		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH	0.35dB	55dB	BLUE
FXLE2-10M*	LOW SMOKE ZERO HALOGEN (LSZH) IEC	10 GbE 50/125um OM3	DUPLEX 1.6mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH	0.30dB	26dB	ELECTRIC IVORY
F5LE2-10M*		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F6LE2-10M*		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F9LE2-10M*		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH	0.35dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX ST TO LC CONFIGURATION CUSTOMER DRAWING		
										 PANDUIT TM CORP. TINLEY PARK, ILL 60477		
										 THIRD ANGLE PROJECTION		
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (1.X) ±.03 (0.8) ANGLES (1.XXX) ±.010 (0.3)		
										DRAWING FILENAME M02779BF_DC_00A.prt		
										SCALE NONE		
										PART NO. SEE TABLE		
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-14					DATE 04-27-07	DRAWING NO. 02779-14 (SHT. 2 of 2)	SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D		