




SPECIFICATION

- 1.Rated Voltage 1.5V
- 2.Operating Voltage 1~2V
- 3.Max.Rated Current 30mA
- 4.Coil Resistance $16 \pm 2 \Omega$
- 5.Coil Impedance 40Ω
- 6.Min.Sound Pressure Level 85dB/10cm
- 7.Resonant Frequency 2800Hz
- 8.Case Material PBT
- 9.Operating Temperature $-20 \sim +70^{\circ}\text{C}$
- 10.Store Temperature $-30 \sim +80^{\circ}\text{C}$
- 11.Weight 2g

				KEPO KEPO ELECTRONIC CO., LTD. http://www.kepo.com.tw			
				Magnetic Buzzer KPM-1201A8			
No.	DESCRIPTION	APPROVED	DATE				
TOLERANCES UNLESS NOTED OTHERWISE X = XX = XXX = 90° FORMED ANGLES ±2° FIRST ANGLE PROJECTION		APPROVALS		DATE			
		DRAWN			UNIT	DWG NO.	
		CHECKED			mm	KP3.840.683	
		APPROVED		04.02.11	SCALE	NOT TO SCALE	VER 1.0