

T120I0K2

Heavy Duty Cable Tie, 120 lb. 11.81" Max. Bun. Dia. 3.15" PA66, Black, 50/pk

Article Number: 111-12201

Part Number: T120I0K2

Type: T120I

Material: PA66




1. Base Data

Part No.	T120I0K2
Type	T120I
Color	Black (BK)
Features	HellermannTyton manufactures a full line of high quality cable ties in a variety of styles, sizes, materials, and colors. HellermannTyton cable ties are engineered and manufactured for maximum performance and quality.
Application	Used to bundle and secure wire and cable.

Application Method	Quick, simple application by hand or with HellermannTyton tensioning tools.
---------------------------	---

2. Product Dimensions



Min. Tensile Strength	120 lbs / 535 N
Length (L)	11.81 " / 300 mm
Width (W)	.30 " / 7.6 mm
Max. Cable Tie Width	0.30 " / 7.61
Min. Ø Bundle	.20 " / 5.0 mm
Max. Ø Bundle	3.15 " / 80.0 mm
Head Length	.393 "
Head Width	.502 "

4. Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Certification	UL Listed
Flammability	UL94 V2
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	

Logistic and Packaging

Packaging Type	bag
----------------	-----

Pkg. Qty.	50
-----------	----

Carton Qty.	1000
-------------	------

UPC	08930605796
-----	-------------


Miscellaneous

UL Listed (US and Canada)	Yes
---------------------------	-----

UL Recognized (US and Canada)	Yes
-------------------------------	-----

Cable Ties

Heavy Duty Cable Ties



Material Data

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C) continuous
Flammability	UL94 V2



T120 Series



File# E64139



File# E64139

File# E04139

File# E04139

Product Selection													
Article No.	Part No.	Type	US Gov. Designation	Min. Tensile Strength		Length (L)		Max. Ø Bundle		Width (W)		Color	Pkg. Qty.
				lbs.	(N)	in.	(mm)	in.	(mm)	in.	(mm)		
T120S													
111-12819	T120S9K2	T120S	—	120 lbs	(535)	8.85"	(225)	2.17"	(55)	.30"	(7.6)	Natural	50
111-12813	T120S9H4	T120S	—	120 lbs	(535)	8.85"	(225)	2.17"	(55)	.30"	(7.6)		500
111-12803	T120S0K2	T120S	—	120 lbs	(535)	8.85"	(225)	2.17"	(55)	.30"	(7.6)	Black	50
111-12808	T120S0H4	T120S	—	120 lbs	(535)	8.85"	(225)	2.17"	(55)	.30"	(7.6)		500
T120I													
111-12211	T120I9K2	T120I	—	120 lbs	(535)	11.81"	(300)	3.15"	(80)	.30"	(7.6)	Natural	50
111-12213	T120I9H4	T120I	—	120 lbs	(535)	11.81"	(300)	3.15"	(80)	.30"	(7.6)		500
111-12201	T120I0K2	T120I	—	120 lbs	(535)	11.81"	(300)	3.15"	(80)	.30"	(7.6)	Black	50
111-12206	T120I0H4	T120I	—	120 lbs	(535)	11.81"	(300)	3.15"	(80)	.30"	(7.6)		500
T120R													
112-12019	T120R9K2	T120R	MS3367-3-9	120 lbs	(535)	15.24"	(387)	4.13"	(105)	.30"	(7.6)	Natural	50
111-12036	T120R9H4	T120R	MS3367-3-9	120 lbs	(535)	15.24"	(387)	4.13"	(105)	.30"	(7.6)		500
112-12060	T120R0K2	T120R	*	120 lbs	(535)	15.24"	(390)	4.13"	(105)	.30"	(7.6)	Black	50
111-12013	T120R0H4	T120R	*	120 lbs	(535)	15.24"	(387)	4.13"	(105)	.30"	(7.6)		500
T120L													
111-12419	T120L9K2	T120L	MS3367-6-9	120 lbs	(535)	30.0"	(760)	8.85"	(225)	.30"	(7.6)	Natural	50
111-12405	T120L0K2	T120L	*	120 lbs	(535)	30.0"	(760)	8.85"	(225)	.30"	(7.6)	Black	50

Installation tools - MK9, MK9HT, MK9P. Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes. *Military black available. Contact HellermannTyton for more information.



File# E64139

T150 Series

Product Selection												
Article No.	Part No.	Type	US Gov. Designation	Min. Tensile Strength	Length (L)		Max. Ø Bundle		Width (W)		Color	Pkg. Qty.
				lbs. (N)	in. (mm)	in. (mm)	in. (mm)	in. (mm)				
T150R												
111-15203	T150R9X2	T150R(U)	—	175 lbs (780)	15.35" (390)	4.13" (105)	.35" (8.8)	Natural	25			
111-15200	T150R0X2	T150R(U)	—	175 lbs (780)	15.35" (390)	4.13" (105)	.35" (8.8)	Black	25			
T150M												
111-15619	T150M9X2	T150M	—	175 lbs (780)	21.00" (530)	5.91" (150)	.35" (8.9)	Natural	25			
111-00124	T150M0X2	T150M	—	175 lbs (780)	21.00" (530)	5.91" (150)	.35" (8.9)	Black	25			
T150L												
111-15419	T150L9X2	T150L	—	175 lbs (780)	32.28" (820)	9.65" (245)	.35" (8.9)	Natural	25			
111-15405	T150L0X2	T150L	—	175 lbs (780)	32.28" (820)	9.65" (245)	.35" (8.9)	Black	25			
T150LL												
111-15719	T150LL9X2	T150LL	—	175 lbs (780)	36.42" (925)	10.83" (275)	.35" (8.9)	Natural	25			
111-15700	T150LL0X2	T150LL	—	175 lbs (780)	36.42" (925)	10.83" (275)	.35" (8.9)	Black	25			
T150XL												
111-15519	T150XL9X2	T150XL	—	175 lbs (780)	43.11" (1095)	13.00" (330)	.35" (8.9)	Natural	25			
111-15500	T150XL0X2	T150XL	—	175 lbs (780)	43.11" (1095)	13.00" (330)	.35" (8.9)	Black	25			
T150XLL												
111-15304	T150XLL9X2	T150XLL	—	175 lbs (780)	52.17" (1325)	15.95" (405)	.35" (8.9)	Natural	25			
111-15300	T150XLL0X2	T150XLL	—	175 lbs (780)	52.17" (1325)	15.95" (405)	.35" (8.9)	Black	25			

Installation tools - MK9, MK9HT, MK9P. Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.