


Amp	Volt	Hz	IP Ident. colour + h	Part No.
				




Plugs and sockets
for extra-low voltages 2 pole
up to 50 V
IEC/EN 60 309



EAN No.
4015609.

16	24~	50/60	-	10 110
	42~	50/60	12	10 111
	42~	100/200	4	10 112
	42~	300	2	10 113
	42~	400	3	10 114
	42~	>400/500	11	10 115
	42 ~	-	10	10 116
32	24~	50/60	-	11 110
	42~	50/60	12	11 111
	42~	100/200	4	11 112
	42~	300	2	11 113
	42~	400	3	11 114
	42~	>400/500	11	11 115
	42 ~	-	10	11 116

wall socket outlets, external fixing means, 1 top cable entry



Ampère	b	c	d	e	f	l	n	Pg
16 A	54,5	5,2	81	70	72	28	119	21
32 A	54,5	5,2	81	70	72	28	119	21

10

169

10




169

003747
003754
003761
003778
003785
003792
003808

005819
121656
005826
005833
005840
005857
005864

16	24~	50/60	-	10 100
	42~	50/60	12	10 101
	42~	100/200	4	10 102
	42~	300	2	10 103
	42~	400	3	10 104
	42~	>400/500	11	10 105
	42 ~	-	10	10 106
32	24~	50/60	-	11 100
	42~	50/60	12	11 101
	42~	100/200	4	11 102
	42~	300	2	11 103
	42~	400	3	11 104
	42~	>400/500	11	11 105
	42 ~	-	10	11 106

wall socket outlets, external fixing means, cable entries: top: 1 x Pg 21,
bottom: 2 x Pg 16



Ampère	b	c	d	e	f	l	n
16 A	80	6,2	93	90	93	60	125
32 A	80	6,2	93	90	93	60	125

10

213

10



213

003679
003686
003693
003709
003716
003723
003730

005741
005758
005765
005772
005789
005796
005802

16	24~	50/60	-	10 280
	42~	50/60	12	10 281
	42~	100/200	4	10 282
	42~	300	2	10 283
	42~	400	3	10 284
	42~	>400/500	11	10 285
	42 ~	-	10	10 286
32	24~	50/60	-	11 280
	42~	50/60	12	11 281
	42~	100/200	4	11 282
	42~	300	2	11 283
	42~	400	3	11 284
	42~	>400/500	11	11 285
	42 ~	-	10	11 286

plugs, flexible cable entry



Ampère	d	e	f	m	n	Op
16 A	135	59	55	99	22,5	8/21
32 A	135	59	55	99	22,5	8/21

10

110

10



110

004379
004386
004393
004409
004416
004423
004430

006441
006458
006465
006472
006489
006496
006502

16	24~	50/60	-	10 210
	42~	50/60	12	10 211
	42~	100/200	4	10 212
	42~	300	2	10 213
	42~	400	3	10 214
	42~	>400/500	11	10 215
	42 ~	-	10	10 216
32	24~	50/60	-	11 210
	42~	50/60	12	11 211
	42~	100/200	4	11 212
	42~	300	2	11 213
	42~	400	3	11 214
	42~	>400/500	11	11 215
	42 ~	-	10	11 216

plugs, gland entry Pg 16



Ampère	d	e	f	m	n	Pg
16 A	128	59	55	99	22,5	16
32 A	128	59	55	99	22,5	16

10

108

10

108

004089
004096
004102
004119
004126
004133
004140

006151
006168
006175
006182
006199
006205
006212