



WATER PROOF SWITCHES

DIMENSIONS

Unless otherwise specified, a tolerance of $\pm 0.4\text{mm}$ applies to all dimensions.



SW (IP67) SERIES

APPLICATIONS :

Automotive Door Latch, Coffee Machine, Steamer, Telephone, Air Conditioner, Humidifier, Alarm, Time Recorder, Security Device, Mixer & Chopper, Solder Gun, Neon Phone, Fax Machine, Joystick, Water Pump, Gas Detector, Pencil Sharpener, Money Sorter, Food Processor, Electric Knife, Toy Car, Juice Maker, Electric Steak Pan

CERTIFICATE INFORMATION

Model Name	UL, cUL	ENEC14
SW-05S	0.1A/5A 30VDC 0.1A/5A 125/250VAC μ T120,1E4	6A 250VAC, μ T70 1E4 (PVC cable) 6A 250VAC, μ T120 1E4 (High heat resistant cable or bare Terminal)

ORDERING INFORMATION

S	W	—	0	5	S	—	0	0	A	0	—	E	A	0	0	1	—	Z															
SERIES PREFIX		C O D E		RATING CURRENT		C O D E		O P E R A T I N G F O R C E		C O D E		A C T U A T O R T Y P E		C O D E		W I R E S I D E		C O D E		C I R C U I T A R R A N G E M E N T		C O D E		A W G T Y P E		C O D E		U L N U M B E R		S E R I A L C O D E		R O H S C O D E	
05		5A:125/250 VAC 6A:125/250 VAC		S		STANDARD		00				A				0		S.P.D.T.		E		20		A		UL1007							
								01				B				1		S.P.S.T. NO		F		22		B		UL1015							
								02				C				2		S.P.S.T. NC		G		24		C		UL1430							
								03				D								H		26		D		UL1061							
								04				E								I		28		F		AV							
								05												J		30											
								06																									
								07																									
								08																									
								09																									