



MULTI-CONDUCTOR CABLE SILVER PLATED COPPER SHIELDED


MIL-W-16878 TYPE E TEFLON® SHIELDED CABLES

DESCRIPTION:

Stranded silver plated copper conductors, insulated with Type E extruded TFE TEFLON, color coded, cabled, braided silver plated copper shield (90% coverage), white TFE TEFLON tape wrapped jacket.

TEMPERATURE RATING:

-65° C to 200° C



OLYMPIC NO.	NO. OF COND.	CONDUCTOR SIZE	CONDUCTOR STRAND	NOM. WALL THICK.	NOM. JACKET THICK.	NOM. O.D.	SUGG. WORK. VOLT.
3416	1	22	19/34	.010"	.010"	.089"	600
3417	2	22	19/34	.010"	.010"	.144"	600
3418	3	22	19/34	.010"	.012"	.156"	600
3419	4	22	19/34	.010"	.012"	.166"	600

3420	1	20	19/32	.010"	.010"	.100"	600
3421	2	20	19/32	.010"	.012"	.162"	600
3422	3	20	19/32	.010"	.012"	.175"	600
3423	4	20	19/32	.010"	.012"	.185"	600

3424	1	18	19/30	.010"	.010"	.113"	600
3425	2	18	19/30	.010"	.012"	.188"	600
3426	3	18	19/30	.010"	.012"	.196"	600
3427	4	18	19/30	.010"	.012"	.215"	600

3428	1	16	19/29	.011"	.012"	.123"	600
3429	2	16	19/29	.011"	.012"	.200"	600
3430	3	16	19/29	.011"	.012"	.218"	600
3431	4	16	19/29	.011"	.014"	.235"	600

COLOR CODE:

- 1 - White
- 2 - White, Black
- 3 - White, Black, Red
- 4 - White, Black, Red, Green

Passes the VW-1 vertical flame test