



Touch Side View



- NOTES:
1. INPUT MODE : PROJECTED CAPACITIVE
 2. OVERALL THICKNESS : 1.75±0.20mm
 3. FRONT SURFACE : CLEAR TYPE
 4. TAIL TYPE : GOLD PLATED FPC , ZIF
 5. OTHER SPEC : SEE APPROVAL SHEET



NO.	DATE	DESCRIPTION	CHK
REVISION			
CHIEF OF DESIGN	Jerry	APPROVED	Alex
ENGINEER		PROJECT MANAGER	
DRAWN BY	Andre	DATE	JAN 11, 2011
SHT 1	OF 1	REV.	

Apex Material Technology Corp.			
TOLERANCES UNLESS SPECIFIED		MODEL NAME : P3008	
.X	± 0.50	DWG NO : P3008-0-012	
.XX	± 0.50		
.XXX	± 0.30		
ANGULAR		SCALE: N/S UNIT: mm	