


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

| REV. | REVISION               |          |          |
|------|------------------------|----------|----------|
|      | DESCRIPTION            | DATE     | APPROVED |
| A    | Changed Pin Out        | 03-12-07 | DP       |
| B    | Updated Specifications | 02-09-12 | LY       |



#### NOTES:

- CABLE: UL2725 24/26AWG  
26AWGx1P+24AWGx2C+ AEB(AL) 65%  
OUTER JACKET: BLACK, OD: 4.5 ± 0.2mm
- CONNECTOR: USB A TYPE MALE  
INSULATOR: WHITE PBT  
PIN G/F  
GOLD PLATED SHELL
- CONNECTOR: MINI USB (B) 5P/M TYPE MALE  
INSULATOR: BLACK PBT  
PIN G/F  
GOLD PLATED SHELL
- PVC MOLDED: COLOR V398 45P BLACK
- ELECTRICAL TEST:  
<1>.100% OPEN SHORT & MISS WIRE TEST  
<2>.INSULATION RESISTANCE: DC400V 10M ohm MIN.  
<3>.CONDUCTOR RESISTANCE: 3 ohm MAX.
- PACKING: 1PC/POLYBAG W/ LABEL

**CONTROLLED**

| Dim<br>range<br>(mm) | Tolerance<br>+/-<br>(mm) | Qualtek Electronics Corp.<br>WCI DIVISION      |                   |                 |
|----------------------|--------------------------|------------------------------------------------|-------------------|-----------------|
|                      |                          | Part Number: 3021021-16                        | RoHS<br>Compliant |                 |
| 0-1                  | 0.15                     | Description:<br>USB 4P(A)/M - USB MINI 5P(B)/M |                   |                 |
| 1-6                  | 0.20                     |                                                |                   |                 |
| 6-18                 | 0.30                     |                                                | UNIT: mm          | REV. B          |
| 18-50                | 0.50                     |                                                |                   |                 |
| 50-120               | 0.70                     | Drawn / Date                                   | Checked / Date    | Approved / Date |
| 120-250              | 0.90                     | B. Grubb<br>01-26-07                           | 01-26-07          | JJH / 01-26-07  |
| 250-500              | 1.20                     |                                                |                   |                 |