





General ordering data

Order No.	1690220000
Part designation	BLZF 3.5/5 SN OR
Version	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 5, 180°, Box
EAN	4008190328719
Qty.	50 pc(s).

System parameters

Conductor connection system	Tension clamp connection
Outgoing direction of conductor	180°
Pitch	3.5 mm
Pitch in inch	0.138 inch
No. of poles	5
No. of rows	1
Screwdriver blade	0.4 x 2.5
Screwdriver blade standard	DIN 5264-A
Stripping length	10 mm
L1 in mm	14 mm
L1 in inch	0.551 inch
Electric shock protection to DIN VDE 0470	IP 20
Electric shock protection to DIN VDE 0470	Safe from finger touch

System parameters

Material data

Insulating material	PBT
Colour	orange
colour chart	Similar to RAL 2000
Insulating material group	IIIa
Flammability class UL 94	V-0
CTI	≥ 200
Contact base material	Copper alloy
Contact surface	tinned

Connectable conductors

Clamping range, min.	0.13 mm ²
Clamping range, max.	1.5 mm ²
AWG, min.	28
AWG, max.	16
Outer diameter of insulation, max.	2.9 mm
Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	1.5 mm ²
Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²
With wire end ferrule, acc. to DIN 46 228/1, min.	0.2 mm ²
With wire end ferrule, acc. to DIN 46 228/1, max.	1.5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.2 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	1 mm ²
Gauge to EN 60999 a x b; $\varnothing$	2.4 mm x 1.5 mm;

DIN IEC rating data

Rated current, min. No. pins (Tu=20°C)	14.5 A
Rated current, max. No. pins (Tu=20°C)	10 A
Rated current, min. No. pins (Tu=40°C)	12 A
Rated current, max. No. pins (Tu=40°C)	8 A
Rated voltage for overvoltage class/pollution severity II/2	320 V
Rated voltage for overvoltage class/pollution severity III/2	160 V
Rated voltage for overvoltage class/pollution severity III/3	160 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	2.5 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	2.5 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	2.5 kV
Short-time withstand current resistance	3 x 1s with 100 A

CSA rating data

Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor (field wiring), min.	26
AWG conductor (field wiring), max.	14

CSA rating data

UL 1059 rating data

Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor, min.	26
AWG conductor, max.	14

Approvals

Approvals institutes



Classifications

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	27-26-07-01
eClass 5.0	27-26-07-01
eClass 5.1	27-26-07-04

Similar products

Order No.	Part designation	Version
1690190000	BLZF 3.5/2 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 2, 180°, Box
1690420000	BLZF 3.5/2 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 2, 180°, Box
1690200000	BLZF 3.5/3 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 3, 180°, Box
1690430000	BLZF 3.5/3 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 3, 180°, Box
1690210000	BLZF 3.5/4 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 4, 180°, Box
1690440000	BLZF 3.5/4 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 4, 180°, Box
1690450000	BLZF 3.5/5 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 5, 180°, Box
1690230000	BLZF 3.5/6 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 6, 180°, Box

1690460000	BLZF 3.5/6 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 6, 180°, Box
1690240000	BLZF 3.5/7 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 7, 180°, Box
1690470000	BLZF 3.5/7 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 7, 180°, Box
1690250000	BLZF 3.5/8 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 8, 180°, Box
1690480000	BLZF 3.5/8 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 8, 180°, Box
1690260000	BLZF 3.5/9 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 9, 180°, Box
1690490000	BLZF 3.5/9 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 9, 180°, Box
1690270000	BLZF 3.5/10 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 10, 180°, Box
1690500000	BLZF 3.5/10 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 10, 180°, Box
1690280000	BLZF 3.5/11 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 11, 180°, Box
1690510000	BLZF 3.5/11 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 11, 180°, Box
1690290000	BLZF 3.5/12 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 12, 180°, Box
1690520000	BLZF 3.5/12 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 12, 180°, Box
1690300000	BLZF 3.5/13 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 13, 180°, Box
1690530000	BLZF 3.5/13 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 13, 180°, Box
1690310000	BLZF 3.5/14 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 14, 180°, Box
1690540000	BLZF 3.5/14 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 14, 180°, Box

1690320000	BLZF 3.5/15 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 15, 180°, Box
1690550000	BLZF 3.5/15 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 15, 180°, Box
1690330000	BLZF 3.5/16 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 16, 180°, Box
1690560000	BLZF 3.5/16 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 16, 180°, Box
1690340000	BLZF 3.5/17 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 17, 180°, Box
1690570000	BLZF 3.5/17 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 17, 180°, Box
1690350000	BLZF 3.5/18 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 18, 180°, Box
1690580000	BLZF 3.5/18 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 18, 180°, Box
1690360000	BLZF 3.5/19 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 19, 180°, Box
1690590000	BLZF 3.5/19 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 19, 180°, Box
1690370000	BLZF 3.5/20 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 20, 180°, Box
1690600000	BLZF 3.5/20 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 20, 180°, Box
1690380000	BLZF 3.5/21 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 21, 180°, Box
1690610000	BLZF 3.5/21 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 21, 180°, Box
1690390000	BLZF 3.5/22 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 22, 180°, Box
1690620000	BLZF 3.5/22 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 22, 180°, Box
1690400000	BLZF 3.5/23 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 23, 180°, Box

1690630000	BLZF 3.5/23 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 23, 180°, Box
1690410000	BLZF 3.5/24 SN OR	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 24, 180°, Box
1690640000	BLZF 3.5/24 SN SW	PCB plug-in connector, Female connectors, Tension clamp connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.50 mm, No. of poles: 24, 180°, Box