


Type	Size	Description	Part No.
Incandescent	T10 (T-3¼)	Miniature wedgebase lamp	(see table)



Drawing not to scale
All dimensions in mm

PHOTOMETRY DATA

Farnell Part No.	SLI P/N	Lamp Rating	Test Volts	Current (mA)			Light Output (Lm)			Fil Shape	Life (Hrs)
				Min	Nom	Max	Min	Nom	Max		
526976	159	6.3V 0.95W	6.3	135	150	165	3.5	4.3	5.1	C-2R	7500
3167884	259	6.3V 1.57W	6.3	225	250	275	6.1	8.2	10.2	C-2R	10000
623430	1112	12V 1.2W	12	90	100	110	3.8	5	6.2	C-2V	5000
620567	521	12V 1.5W	12	106	125	144	4.0	5.5	6.6	C-2V	5000
620555	509	12V 2W	13.5	141	156	171	10.4	13	15.6	C-2V	3000
329034	510	12V 2.2W	13	168	192	216	9.4	12.6	15.7	C-2V	3000
329046	512	12V 2.6W	13	168	200	237	19	22.6	26.2	C-2V	1000
573280	504	12V 3W	13.5	189	222	255	15.4	22	28.6	C-2V	1500
573279	501	12V 5W	13.5	333	370	407	40	50	60	C-2R	1000
329058	161	14V 2.66W	14	171	190	209	10	12.5	15	C-2F	4000
653858	194	14V 3.78W	14	243	270	297	20	25	30	C-2F	2500
653860	168	14V 4.9W	14	315	350	385	30	37.6	45	C-2F	1500
329060	513-002	24V 2W	28	85	95	104	9.8	13	16.2	C-2F	5000
573292	505	24V 3W	28	122	143	164	15.4	22	28.6	C-2F	1000
573309	507	24V 5W	28	225	250	275	40	50	60	C-2F	1000
329071	656-002	28V 1.7W	28	54	60	66	5.9	7.8	9.7	C-2F	5000

NOTES:

- 1) W2.1x9.5d in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-91-x.
- 2) Bulb glass to be durably marked with rating and trademark.