

## VGA + Audio to HDMI Adapter Cable with USB Power, 1920 x 1080 (1080p) @ 60 Hz (M/M), 6 ft.

MODEL NUMBER: **P116-006-HDMI-A**



All-in-one solution converts analog VGA video and 2-channel audio for display on an HDMI monitor, projector or TV without having to upgrade your source device. Recommended for digital signage and media presentations.

### Description

The P116-006-HDMI-A VGA + Audio to HDMI Adapter Cable (M/M) saves you money on costly computer upgrades by converting a VGA video + audio signal for display on an HDMI monitor, projector or television. You can display a rich high-definition (HD) signal in your home theater setups, media presentations or digital signage using your tried-and-true analog source equipment. The cable is ready to use right from the box with no software or drivers to install. It's powered via the built-in USB cable, so no external power supply is required.

This six-foot cable supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz. Connect the VGA plug to your computer's VGA port, the built-in 3.5 mm stereo plug to your computer's audio jack, and the built-in USB cable to a USB port on your computer or a USB charger. Then, connect the HDMI plug to your display's HDMI input port. The P116-006-HDMI-A complies with HDCP 1.2 and HDMI 1.3 standards. Corrosion-resistant gold-plated connectors and contacts provide maximum conductivity and minimize data loss.

### Features

#### Converts VGA Video + Audio to HDMI

- Recommended for home theaters, media presentations and digital signs
- Saves money by allowing you to use existing analog source equipment without any expensive upgrades
- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Compliant with HDCP 1.2 and HDMI 1.3
- Gold-plated connectors and contacts for maximum conductivity and minimum data loss

### Highlights

- Saves money by eliminating need to update expensive equipment
- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Bus-powered via USB connection
- Compliant with HDCP 1.2 and HDMI 1.3
- Plug and play—no software or drivers to install

### System Requirements

- Source device with VGA, 3.5 mm and USB ports
- Display device with HDMI port

### Package Includes

- P116-006-HDMI-A VGA + Audio to HDMI Adapter Cable (M/M), 6 ft.
- Quick Start Guide

#### Plug-and-Play Convenience

- Ready to use right from the box—no software or drivers required
- Connects easily to source's VGA, 3.5 mm audio and USB ports and display's HDMI port
- Bus-powered via USB connection—no external power supply required

## Specifications

OVERVIEW	
UPC Code	037332203342
Technology	HDMI (All types); Stereo Audio; USB (all versions); VGA/SVGA
INPUT	
Cable Length (ft.)	6
Cable Length (in.)	72
PHYSICAL	
Unit Weight (lbs.)	0.3
Unit Weight (kg)	0.14
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	10% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HD15 (MALE)
Side B - Connector 2	3.5MM (MALE)
Side B - Connector 3	USB A (MALE)
FEATURES & SPECIFICATIONS	
HDMI Specification	1.3
HDCP Specification	1.2
WARRANTY	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	2-year limited warranty
--	-------------------------

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>