



DIMENSIONS (mm)



Cap Type: E27 -IEC60061-1 sheet -7004-21
Cap Type: B22d -IEC60061-1 sheet -7004-10

ELECTRICAL DATA¹

		<u>Nominal Value</u>	<u>Min.</u>	<u>Max.</u>
Lamp rated wattage	(W) :	15		16.5
Lamp operating voltage ac 50/60Hz (rms)	(V) :	220-240		
Lamp current ac 50/60Hz (rms)	(mA) :	110		

OPERATING CONDITIONS:

		<u>Nominal Value</u>	<u>Min.</u>	<u>Max.</u>
Cap Rim temperature	(°C) :			80
Lamp Ambient Temperature	(°C) :	25	-15	
Starting time at 25°C	(s) :			<2.0
Operating Position	:	Unrestricted		
Weight	(g) :	80		

LAMP LIFE²

Average life (IEC Test Cycle) (h) : 10000

PHOTOMETRIC DATA:

	<u>colour no.</u>	<u>Luminous Flux nominal value (lm)</u>	<u>CRI (Class)</u>	<u>Colour Temp. (K)</u>	<u>Energy Efficiency Class</u>	<u>ILCOS Code</u>
Homelight Deluxe	827	900	1b	2700	A	FBT-15/27/1b-E27-48/112
Homelight Deluxe	827	900	1b	2700	A	FBT-15/27/1b-B22-48/112
Cool White Deluxe	840	900	1b	4000	A	FBT-15/40/1b-E27-48/112
Cool White Deluxe	840	900	1b	4000	A	FBT-15/40/1b-B22-48/112

Attention:

Lamps comply with EN 60 968 (Safety Requirements) and EN 60 969 (Performance Requirements) and CE Regulations.

¹Measured according to EN 60 969, at 50 Hz, lamp aged 100h

²Life test according to EN 60 969

Issued by : Havells Sylvania UK Ltd
Date : 27.04.2009
Revision Date :

DATA SHEET

Specification No. : N3004
Supersedes :
Page : 1 of 1