


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	B2	OBSOLETING PART NUMBERS 15 POSITION AND ABOVE		09APR2015	CR	PS

MATERIAL:
HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN PLATE, COPPER ALLOY.
SCREWS: 6-32, STEEL, ZINC PLATED AND CLEAR CHROMATE.


ELECTRICAL:
UL CLASS C: 20A, 150V.
UL CLASS D: 10A, 300V.
CSA TYPE B: 20A, 300V.
CSA TYPE C: 20A, 300V.
CSA TYPE D: 10A, 300V.
CSA TYPE E: 20A, 300V.
WIRE RANGE: 12-22 AWG.

MECHANICAL:
OPERATING TEMP.: -40°C TO +105°C.
RECOMMENDED TIGHTENING TORQUE: 7 IN-LBS.

- 1 TRIMMED TO LENGTH.
- 2 PRELIMINARY PART NUMBER.
- 3 OBSOLETE PARTS.



3	9.815	30	4DB-R108-30	3-1546462-0
3	9.490	29	4DB-R108-29	2-1546462-9
3	9.165	28	4DB-R108-28	2-1546462-8
3	8.840	27	4DB-R108-27	2-1546462-7
3	8.515	26	4DB-R108-26	2-1546462-6
3	8.190	25	4DB-R108-25	2-1546462-5
3	7.865	24	4DB-R108-24	2-1546462-4
3	7.540	23	4DB-R108-23	1437668-7
3	7.215	22	4DB-R108-22	2-1546462-2
3	6.890	21	4DB-R108-21	2-1546462-1
3	6.565	20	4DB-R108-20	7-1437667-8
3	6.240	19	4DB-R108-19	1-1546462-9
3	5.915	18	4DB-R108-18	1-1546462-8
3	5.590	17	4DB-R108-17	1-1546462-7
3	5.265	16	4DB-R108-16	1-1546462-6
3	4.940	15	4DB-R108-15	7-1437667-7
	4.615	14	4DB-R108-14	1-1546462-4
	4.290	13	4DB-R108-13	1-1546462-3
	3.965	12	4DB-R108-12	1-1546462-2
	3.640	11	4DB-R108-11	1-1546462-1
	3.315	10	4DB-R108-10	1-1546462-0
	2.990	9	4DB-R108-09	1546462-9
SEE FIGURE	2.665	8	4DB-R108-08-085	7-1437667-6
	2.665	8	4DB-R108-08	1546462-8
	2.340	7	4DB-R108-07	1546462-7
	2.015	6	4DB-R108-06	7-1437667-5
	1.690	5	4DB-R108-05	7-1437667-4
	1.365	4	4DB-R108-04	7-1437667-3
	1.040	3	4DB-R108-03	7-1437667-2
SEE FIGURE 2	.715	2	4DB-R108-02-107	3-1546462-1
	.715	2	4DB-R108-02	7-1437667-1
	DIM A	NO OF POS	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 1/21/03	 TE Connectivity					
		CHK S YODER 1/21/03						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± .005 4 PLC ± - ANGLES ± 2'	APVD S YODER 1/21/03	NAME 4DB SERIES R108 STYLE -					
		PRODUCT SPEC -						
		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
		WEIGHT -	A3	00779	C-7-1437667-1		-	
MATERIAL -	FINISH -	CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1	REV B2