

BMP® 71 LABEL PRINTER

The All-In-One Labeler For Your Whole Crew



Catalog #	Description
BMP71*	BMP71 Label Printer
BMP71-LM	BMP71 Label Printer with LabelMark Software
BMP71-MW	BMP71 Label Printer with Markware Lean Software
BMP71-360-KIT	BMP71 Label Printer with Brady 360 Replacement Program
BMP71-QC	BMP71 Label Printer with Quick Charger
BMP71-SC	BMP71 Label Printer with Soft Case
BMP71-SC-QC	BMP71 Label Printer with Soft Case and Quick Charger
M71-AC-BC	BMP71 AC/Battery Adaptor
M71-ADAPT	TLS/Handimark Media Adaptor
M71-BATT	BMP71 Battery Pack
M71-CABLE	BMP71 USB Cable
M71-CLEAN	BMP71 Cleaning Kit
M71-HC	BMP71 Hardcase
M71-QC	BMP71 Quick Charger
M71-SC	BMP71 Softcase
BMP71-360	Brady 360 Replacement Printer Program

*Label printer ships with Hardcase, Charger/AC Adapter, 1 Roll of M71-31-423 White Die Cut Labels, 1 M71-R6000 Black Ribbon Cartridge, Roll Adapter, Rechargeable Battery, USB Cable, Quickstart Guide, a CD including the Printer Driver, Users Guide and Tutorial.

Catalog #	Description
Applications	Arc Flash Labeling, Barcode Labeling, Circuit Board Labeling, Data Comm Labeling, Facility, Safety & Maintenance ID, General & Industrial Labeling, Healthcare ID, Laboratory ID, Lockout Tagout Labeling, Panel ID, Product ID, Security ID, Wire & Cable Marking
Print Technology	Thermal Transfer
Print Resolution	300dpi
Print Speed	1.5" per second
Color Capability	Single color print
Max Labels per day	1,000
Keyboard	Full QWERTY
Portability	Yes
Weight	5.49lbs with battery
Dimensions	13.100 in x 9.500 in x 4.600 in
Power Supply	Rechargeable battery or AC power
PC Connectivity	Yes
Stand Alone Printing	Yes
Connectivity Options	USB
Continuous vs. Die Cut	Can print both continuous and die cut labels
Materials Supported	Continuous, die-cut, bulk, over 400 stock parts, custom parts available
Tape Widths	Various sizes from .25 - 2"
Max Label Width	2"
Max Print Width	1.75"
Label Roll Length	50' (500' bulk supplies)
Text sizes	4 to 170pt.
Multi-Line Print	Yes
Print Rotation	Yes
Serialization	Yes
Barcode	39 and 128
Warranty	12 Months - See Terms and Conditions